

WW-CP-201P PRINTED ALL-WEATHER CORROSION PROTECTION TAPE - 10MIL

DESCRIPTION			FEATURES			
WW-CP-201P is a prinited,10 mil plasticized PVC tape with superior adhesion and corrosion protection. This tape can be used to protect against abrasion, corrosion, and impact on metal pipes, conduit, and fittings. It is suitable for use above and below ground.				 Black PVC backing Excellent adhesion Printed Great protection in all weather conditions 		
MATERIALS	BACKING	ADHESIVE	COLOR	STANDARD SIZES (WIDTH X LENGTH)	PART NUMBER	
	Plasticized PVC	Rubber based	Black - Printed	2" x 100' (51mm x 30.5m)	WW-CP-201P	
TECHNICAL PROPERTIES	CHARACTERISTIC	TYPICAL VALUE		TEST METHOD		
	Thickness (mils)	10		ASTM D 1000		
	Breaking strength (lbs/in)	20		ASTM D 1000		
	Elongation at break (%)	200		ASTM D 1000		
	Adhesion to steel (oz/in)	20		ASTM D 1000		
	Adhesion to backing (oz/in)	20		ASTM D 1000		
	Dielectric strength (V/mil)	700		ASTM D 1000		
RECOMMENDED USES		STORAGE		SHELF LIFE		
For protection against abrasion, corrosion, and impact, both above and below ground.		In original packaging, placed in horizontal position under cover and temperature between 5°C and 35°C.		60 months from date of manufacture.		

Data in table represents average test results and are not to be used for specification purpose. The product users should make their own tests to determine the products' suitability for the intended use

LIMITED WARRANTY: NSi Industries LLC warrants that each of its products will be free from material and manufacture defects at the date of shipment (unless specified otherwise). NSi Industries LLC makes or gives no warranty to the distributor, its customers, or the product's end user regarding the product's merchantability and/or suitability for their/its intended use or purpose, and buyer shall assume all risks associated therewith. Provided that the product is proven to be defective, NSi Industries sole obligation and buyer's exclusive remedy shall be through the distributor, at NSi Industries' discretion, to replace, repair, or refund the product proved to be defective within the time period specified above. EXCEPT AS EXPRESSLY SET FORTH HEREIN, NSI INDUSTRIES MAKES OR GIVES NO OTHER WARRANTIES, EXPRESSED OR IMPLIED. Except where prohibited by law, NSi Industries LLC will not be liable for collateral, consequential, indirect or incidental damages arising out of, or connected in any way with the supply of products.