



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WWCYCJ 18-10AWG Ylw Winged Wire Conn

Nsi Industries

Catalog Number	WWCYCJ
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-Y-CJ 100-Count Small Jar Of Yellow Winged Wire Connectors Are Designed For Use On Copper Wires In The 18-10 Awg Size Range. Theyâ€™re Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywher
Weight per unit	0.4880 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Yellow
Finish	Thermoplastic
Housing Material	Thermoplastic

Dimensions and Weight

Size	H=1.01 - W=.717 - ID=.252
------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	18-10AWG YLW WINGED WIRE CONN
extra long description	NSI WWC-Y-CJ Winged Yellow East Twi
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in
Long Description	The Easy-Twist WWC-Y-CJ 100-Count Small Jar of Yellow Winged Wire Connectors are designed for use on copper wires in the 18-10 AWG size range. They are made of flame-retardant thermoplastic rated for a maximum temperature of 105°C (221°F Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere
Product Type	Winged Yellow East Twist, 18-10 Awg - Small Jar Of 100
Special Features	Winged Yellow Wire Connector - 100 Pcs Jar

Manufacturer Information

Brand	Easy-Twist
GTIN	00662381142320
Manufacturers Part Number	WWC-Y-CJ
UPC	662381142320

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Winged Wire Connectors

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.488

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C