



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1026 North Collins Blvd
70433-0000, LA Covington
Phone: 985-302-3016
Fax: 985-249-6076



WWCGRSJ 14-12AWG GRN Winged Wire Conn

Nsi Industries

Catalog Number	WWCGRSJ
Manufacturer	Nsi Industries
Description	The Easy-Twist WWC-GR-SJ 100-Count Small Jar Of Green Winged Wire Connectors Are Designed For Grounding Copper Wires In The 14-12 Awg Size Range. They Have A Hole In The Top Designed For A Through-Wire and Are Made Of Flame-Retardant Thermoplastic. The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Swept-Back Wing Design and Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You
Weight per unit	0.7900 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Green
Finish	Thermoplastic
Housing Material	Thermoplastic

Dimensions and Weight

Depth	.327
Height	1.13
Size	H=1.13 - W=.795 - ID=.327



Descriptions

Description	14-12AWG GRN WINGED WIRE CONN
extra long description	NSI WWC-GR-SJ Winged Grounding Easy
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The GR line includes a hole in the top of the connector for a through wire, for use in grounding applications. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. T
Long Description	The Easy-Twist WWC-GR-SJ 100-Count Small Jar of Green Winged Wire Connectors are designed for grounding copper wires in the 14-12 AWG size range. They have a hole in the top designed for a through-wire and are made of flame-retardant thermoplastic. The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic swept-back wing design and ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you
Product Type	Winged Grounding Easy Twist Connector - Standard Jar Of 100
Special Features	UL 486C

Manufacturer Information

Brand	NSI
GTIN	00662381142504
Manufacturers Part Number	WWC-GR-SJ
UPC	662381142504

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Winged Wire Connectors

Packaging

Carton	1
Weight Per jar	0.79

Uses, Certifications, and Standards

Application	Grounding Wire
environmental conditions	105 C
standard	UL 467