


Specifications



Photo is representative



Eaton X37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, X shape, 1"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	X37 SA
UPC	782274746111
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	2.25 in
PRODUCT WEIGHT	1.1 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS [IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - X37 SA](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Product specifications

SHAPE	X
TRADE SIZE	1"
MATERIAL	Copper-free aluminum



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.




© 2025 Eaton. All Rights Reserved.

Specifications



Photo is representative



Eaton X37 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, X shape, 1"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	X37 SA
UPC	782274746111
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	2.25 in
PRODUCT WEIGHT	1.1 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Resources

CATALOGS [Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

INSTALLATION INSTRUCTIONS [IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS [Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - X37 SA](#)

TECHNICAL SERVICE BULLETINS [Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Product specifications

SHAPE	X
TRADE SIZE	1"
MATERIAL	Copper-free aluminum



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.