

# Eaton XBUT35

Catalog Number: XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A



## General specifications

|                             |                      |
|-----------------------------|----------------------|
| Product Name                | Catalog Number       |
| Eaton XB IEC terminal block | XBUT35               |
| UPC                         | Product Length/Depth |
| 782116905065                | 2.37 in              |
| Product Height              | Product Width        |
| 2.88 in                     | 0.63 in              |
| Product Weight              | Warranty             |
| 0.02 lb                     | 1 year               |
| Certifications              |                      |
| CSA Certified               |                      |
| UL Listed                   |                      |

Type

IEC-XB Series

Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

Voltage rating

IEC 800V, EN 700V, UL 600V

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[XBUT35 3D Model Xchange](#)

[XBUT35 AutoCAD 2D Footprint \(mm\)](#)

[XBUT35 AutoCAD 2D Footprint](#)

[XBUT35 3D Inventor](#)

[XBUT35 2D PDF](#)

[XBUT35 2D Drawing Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT35](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)

# Eaton XBUT35

Catalog Number: XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm<sup>2</sup> maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A



## General specifications

|                             |                      |
|-----------------------------|----------------------|
| Product Name                | Catalog Number       |
| Eaton XB IEC terminal block | XBUT35               |
| UPC                         | Product Length/Depth |
| 782116905065                | 2.37 in              |
| Product Height              | Product Width        |
| 2.88 in                     | 0.63 in              |
| Product Weight              | Warranty             |
| 0.02 lb                     | 1 year               |
| Certifications              |                      |
| CSA Certified               |                      |
| UL Listed                   |                      |

| defaultTaxonomyAttributeLabel           | Resources                                                                                     |
|-----------------------------------------|-----------------------------------------------------------------------------------------------|
| Type                                    | Brochures                                                                                     |
| IEC-XB Series                           | <a href="#">XB IEC TERMINAL BLOCKS</a>                                                        |
|                                         | <a href="#">XB IEC terminal blocks—versatility, quality, and reliability</a>                  |
| Amperage Rating                         | Catalogs                                                                                      |
| 527 (IEC), 40A (EN), 50A (EN), 50A (UL) | <a href="#">Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions</a> |
| Voltage rating                          | Drawings                                                                                      |
| IEC 800V, EN 700V, UL 600V              | <a href="#">XBUT35 3D Model Xchange</a>                                                       |
|                                         | <a href="#">XBUT35 AutoCAD 2D Footprint (mm)</a>                                              |
|                                         | <a href="#">XBUT35 AutoCAD 2D Footprint</a>                                                   |
|                                         | <a href="#">XBUT35 3D Inventor</a>                                                            |
|                                         | <a href="#">XBUT35 2D PDF</a>                                                                 |
|                                         | <a href="#">XBUT35 2D Drawing Xchange</a>                                                     |
|                                         | Specifications and datasheets                                                                 |
|                                         | <a href="#">Eaton Specification Sheet - XBUT35</a>                                            |



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)