Specifications



Eaton XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm2 maximum wire

General specifications	
PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBNL24
UPC	782116905263
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.



Product specifications Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse AMPERAGE RATING 10A (IEC), 10A (UL) VOLTAGE RATING UL 400V

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	XBUT6FBNL24

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.













Specifications



Eaton XBUT6FBNL24

Eaton XB IEC terminal block, Fuse Terminal Blocks with LED 12-30V, 1-2.5 mA, Black, 8 AWG/6 mm2 maximum wire

General specifications	
PRODUCT NAME	Eaton XB IEC terminal block
CATALOG NUMBER	XBUT6FBNL24
UPC	782116905263
PRODUCT LENGTH/DEPTH	1.85 in
PRODUCT HEIGHT	2.17 in
PRODUCT WIDTH	0.32 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	As disconnect terminal block 500V, as fuse terminal block 400V.



Product specifications Screw Connection Fuse Terminal Blocks for 6.3 x 32 mm Fuse AMPERAGE RATING 10A (IEC), 10A (UL) VOLTAGE RATING UL 400V

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	XBUT6FBNL24

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.











