



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XBUT25PE 5.2MM Ground Block 26-12awg

Eaton Corp

Catalog Number	XBUT25PE
Manufacturer	Eaton Corp
Description	Screw Connection Single Level-Through-Feed, #26 Awg Conductor Size, #12 Awg/2.5 SQ.MM Conductor Size, Green/Yellow Insulation Color, 0.205 In Overall Length, 1.85 In Overall Height, 0.03 LB
Weight per unit	0.0300 (lbs/each)
Product Category	Terminal Blocks & Accessories

Features

dimensions	5.2070millimetreXX46.9900millimetre
Maximum Wire Size	12 AWG/2.5 mm ²
Wire Size	IEC #26-12 AWG, EN #26-12 AWG, UL #26-12 AWG

Material, Color, and Finish

Color	GREEN/YELLOW
-------	--------------

Descriptions

Description	5.2MM GROUND BLOCK 26-12AWG
-------------	-----------------------------

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116904860
UPC	782116904860

Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCKS POWER DIST BLOCKS
igcc	4547
Type	IEC-XB Series
unspsc code	39121410

Packaging

Carton	1
Package	50
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Wiring Management and Devices
standard	UL Listed; CSA Certified



Powering Business Worldwide

pe.eaton.com

Screw connection single level-through-feed

XBUT25PE

UPC:782116904860

Dimensions:

- **Height:** 1.85 IN
- **Length:** .205 IN
- **Width:** X

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Maximum Wire Size:** 12 AWG/2.5 mm²
- **Wire Size:** (3) #26-12 AWG
- **Color:** Green/yellow

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT25PE](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data

