ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104



YA28 4/0 Cop 1H Lug

Burndy LLC

Catalog Number	YA28
Manufacturer	Burndy LLC
Description	4/0 Awg Cu, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, Ul/Csa, 90 C, Up to 35KV, Purple Color Code, 15 Die Index.
Weight per unit	0.1300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	15
Material	Copper
Number of Pad Holes	1
Voltage Rating	35 kV

Material, Color, and Finish

Color Code	PURPLE

Descriptions

Description	4/0 COP 1H LUG
extra long description	BUR YA28 CUHYLUG 4/0 1/2STUD
Long Description	4/0 AWG CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV,PURPLE Color Code, 15 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 1-11/16 IN, Die Index: 15, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W28VT, W28RT Die, (4), X28RT Die, (6), Hydraulic: BCT500HS, Y500CTHS Tool, W28VT, W28RT Die, (4), X28RT Die, (6), Y35, Y39, Y750, PAT750 Tool, U28RT Die, (2), Y46 Tool, U28RT Die With PUADP-1 Adapter, (2)

Manufacturer Information

Brand	BURNDY
GTIN	00781810503409
Manufacturers Part Number	YA28
UPC	781810503409

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104

Packaging

Carton	1
Package	10
Weight Per each	0.13

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B