



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XTSC001BBA MMC FVNR 0.63-1A B-MMP B-Cont 1NO 110/50 120/60

Eaton Corp

Catalog Number	XTSC001BBA
Manufacturer	Eaton Corp
Description	Eaton XT IEC Motor Control, Full Voltage Non-Reversing, Combined With A 45 MM B-Frame, 7 to 15A IEC Contactor, Short Circuit Release: 3.5A, Factory-Assembled, B-Frame, 380V/50 HZ, 440V/60 HZ Coil, 1NO-1NC, 3-Phase
Weight per unit	0.0010 (lbs/each)
Product Category	Manual Starters

Features

dimensions	3.7700 IN X 1.7700 IN X 6.0000 IN
------------	-----------------------------------

Descriptions

Description	MMC FVNR 0.63-1A B-MMP B-CONT 1NO 110/50 120/60
extra long description	ETN XTSC001BBA MMCFVNR 0.63-1A B-MM
Features	Eaton's XT line brings IEC power control to a whole new level. The XT IEC series includes non-reversing and reversing contactors and starters as well as overload relays and accessories. Enclosed control options include metallic and non-metallic enclosures with circuit breakers, and North American or European fuses. Save space and engineering design time with XT IEC series overload relays.
Long Description	Eaton XT IEC motor control, Full Voltage Non-Reversing, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 3.5A, Factory-assembled, B-frame, 380V/50 Hz, 440V/60 Hz coil, 1NO-1NC, 3-phase
Product Type	MMCFVNR 0.63-1A B-MMP B-Cont 1NO 110/50

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116602384
Manufacturers Part Number	XTSC001BBA
UPC	782116602384

Taxonomies, Classifications, and Categories

Category Description	IEC/FREEDOM CONTACTOR
Type	Motor Control

Packaging

Carton	1
Weight Per each	0.001



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Safety and Security Systems

standard

IEC 60947,UL 508,UL Listed file E245398,CSA file No. 229767,
Class 3211-05,CE Marked,DIN VDE 0600