

# Specifications



## Eaton XTSC2P5BBA

Eaton XT IEC Full Voltage Non-Reversing Manual Combination Motor Controller, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 224A, Factory-assembled, B-frame, 600V/60 Hz coil, 1NO-1NC, Three-phase, 16A, 110V 50

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC motor control
<b>CATALOG NUMBER</b>	XTSC2P5BBA
<b>UPC</b>	782116603640
<b>PRODUCT LENGTH/DEPTH</b>	3.77 in
<b>PRODUCT HEIGHT</b>	7.03 in
<b>PRODUCT WIDTH</b>	1.77 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>COMPLIANCES</b>	CE Marked DIN VDE 0600
<b>CERTIFICATIONS</b>	UL 508 IEC 60947 CSA file No. 229767, Class 3211-05 UL Listed file E245398
<b>GLOBAL CATALOG</b>	XTSC2P5BBA



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	2.50A
<b>FRAME SIZE</b>	45 mm
<b>COIL</b>	110-120 Vac, 50/60 Hz

## Resources

CATALOGS	<a href="#">Original Equipment Manufacturer, Motor Control and Protection, Volume 9, Tab 2</a> <a href="#">Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTSC2P5BBA</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton XTSC2P5BBA

Eaton XT IEC Full Voltage Non-Reversing Manual Combination Motor Controller, Combined with a 45 mm B-frame, 7 to 15A IEC contactor, Short circuit release: 224A, Factory-assembled, B-frame, 600V/60 Hz coil, 1NO-1NC, Three-phase, 16A,110V 50

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC motor control
<b>CATALOG NUMBER</b>	XTSC2P5BBA
<b>UPC</b>	782116603640
<b>PRODUCT LENGTH/DEPTH</b>	3.77 in
<b>PRODUCT HEIGHT</b>	7.03 in
<b>PRODUCT WIDTH</b>	1.77 in
<b>PRODUCT WEIGHT</b>	0.001 lb
<b>COMPLIANCES</b>	CE Marked DIN VDE 0600
<b>CERTIFICATIONS</b>	UL 508 IEC 60947 CSA file No. 229767, Class 3211-05 UL Listed file E245398
<b>GLOBAL CATALOG</b>	XTSC2P5BBA



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	2.50A
<b>FRAME SIZE</b>	45 mm
<b>COIL</b>	110-120 Vac, 50/60 Hz

## Resources

CATALOGS	<a href="#">Original Equipment Manufacturer, Motor Control and Protection, Volume 9, Tab 2</a> <a href="#">Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTSC2P5BBA</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.

