



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA3CTC38 Ya3ctc38 *Burndy LLC*

Catalog Number	YA3CTC38
Manufacturer	Burndy LLC
Description	3 Awg Cu, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/Csa, 90 C, Up to 35KV, White Color Code, 9 Die Index.
Weight per unit	0.0350 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	9
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	WHITE
------------	-------

Descriptions

Description	YA3CTC38
extra long description	BUR YA3CTC38 CU HYDENT- 3STR-3/8 IN
Long Description	3 AWG CU, One Hole, 3/8 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kv, WHITE Color Code, 9 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Tongue Angle: Straight, Wire Strip Length: 1-1/2 IN, Die Index: 9, Color Code: White, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W3CRT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W3CRT Die, (2), Y35, Y39, Y750, PAT750 Tool, U3CRT Die, (2), Y46 Tool, U3CRT Die With PUADP-1 Adapter, (2), Dieless Tools (number Of Cri

Manufacturer Information

Brand	BURNDY
GTIN	00781810019627
Manufacturers Part Number	YA3CTC38
UPC	781810019627

Taxonomies, Classifications, and Categories

Type	Long Barrel, Tin Plated
------	-------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.035

Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B