



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YGHC26C2 Yghc26c2 Burndy LLC

Catalog Number	YGHC26C2
Manufacturer	Burndy LLC
Description	Copper Compression C Connector, 1 - 2/0 Awg(STR), 3/8" Rod (Run) & 6 Awg(Sol)- 2 Awg(STR) (Tap).
Weight per unit	0.1300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	Run: 2/0, 1 AWG, 35, 70 MM
Die Index	O
Material	Copper
pallet quantity	14800
Tap Size	2, 6 AWG, 10, 35 MM

Material, Color, and Finish

Finish	Unplated
--------	----------

Descriptions

Description	YGHC26C2
extra long description	BUR YGHC26C2 1-2/0 TO 6-2 CU GRD C
Long Description	Copper Compression C Connector, 1 - 2/0 AWG(Str), 3/8" Rod (Run) & 6 AWG(Sol)- 2 AWG(Str) (Tap).
Product Type	Compression
Special Features	Features: Irreversible Compression Ground Tap Figure C Connectors, Accommodates All Cable Combinations From #6 AWG Solid Through 500 KCMIL, C- Shaped Opening Permits Placing Two Continuous Parallel Cables Into Conductor Groove, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Prefilled With PENETROX Compound And Strip Sealed, Certain Sizes Are Also UL467 Listed And CSA Certified For Wire To Ground Rod, Tools, Die Set Catalog Number, And (number Of Crimps): HYPRESS: Y35, Y39, Y750, PAT750 To

Manufacturer Information

Brand	Burndy Canada
GTIN	00781810221020
Manufacturers Part Number	YGHC26C2
sub brand	HYPRESS
UPC	781810221020

Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Taps



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.13

Uses, Certifications, and Standards

Application	For Direct Burial In Earth Or Concrete
standard	Direct Burial