



## Oversize blank box mounted wallplates

## Product description


1-Gang, 2-Gang




1-Gang




2-Gang



2-Gang toggle &amp; duplex receptacle



1-Gang with 0.375" hole



GFER



2160



231



153

## Blank - box mounted

| Description | Material                | Color suffix | Catalog no. |   |   |
|-------------|-------------------------|--------------|-------------|---|---|
| 1-Gang      | Thermoset               | V, W         | □ 2729__    | • | • |
|             | 302/304 stainless steel | —            | □ 93851     | • | • |
| 2-Gang      | 302/304 stainless steel | —            | □ 93852     | • | • |

## Oversize combination wallplates

## Product description

2-Gang

## Combination 2-gang

| Description                | Material  | Color suffix | Catalog no. |   |   |
|----------------------------|-----------|--------------|-------------|---|---|
| Toggle & duplex receptacle | Thermoset | B, V, W      | □ 2148__    | • | • |

## Oversize telephone &amp; coax wallplates

## Product description

2-Gang

## Telephone &amp; coax

| Description                    | Material                | Color suffix | Catalog no. |   |   |
|--------------------------------|-------------------------|--------------|-------------|---|---|
| 1-Gang with 0.37" (9.5mm) hole | Thermoset               | V, W         | □ 2728__    | • | • |
|                                | 302/304 stainless steel | —            | □ 93896     | • | • |

## Wallplate accessories

## Product description

GFCI extension ring, adapters, wallplate screws &amp; pilot light lamp holder

## Wallplate accessories

| Description                                                                                   | Material                | Color suffix     | Catalog no. |   |   |
|-----------------------------------------------------------------------------------------------|-------------------------|------------------|-------------|---|---|
| GFCI extension ring for use with GFCIs, 7/8" spacer (cULus)                                   | —                       | B, BLK, LA, V, W | □ GFER-__** | • |   |
| Adapter - decorator to blank                                                                  | —                       | B, LA, V, W      | □ 2160__    | • | • |
| Adapter - decorator to toggle                                                                 | —                       | V, W             | □ 2161__    | • | • |
| Toggle & receptacle wallplate screws #6-32 x 1/2" (12.7mm) for toggle & receptacle wallplates | Baked enamel head/metal | B, LA, V, W      | □ 231__     |   | • |
|                                                                                               | Nylon                   | RD, V, W         | □ 232__     |   | • |
| Toggle & receptacle wallplate screws #6-32 x 5/16" (7.9mm) for toggle & receptacle wallplates | Baked enamel head/metal | LA, V, W         | □ 2231__    |   | • |
| Recessed pilot light lamp holder with 6 watt clear S-6 bulb (cULus)                           | —                       | —                | □ 153__**†  | • | • |

\*For use with louver wallplate, \*\* cULus Listed, † UL Listed, CSA certified

## Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: B (Brown), BLK (Black), LA (Light Almond), RD (Red), V (Ivory), W (White)

|         |         |              |       |         |         |                   |
|---------|---------|--------------|-------|---------|---------|-------------------|
|         |         |              |       |         |         |                   |
| (Brown) | (Black) | (Lt. Almond) | (Red) | (Ivory) | (White) | (Stainless Steel) |

**Certification information:** 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

**Compliances, specifications and availability are subject to change without notice.**



Indicates NAFTA compliant - Page Q-30



RoHS compliant - Page Q-30