



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F25T8SP35ECO 25W T8 36" 3500K 78 Cri Bi-Pin Energy Saving

*Ge By Current Lamps*

|                  |                                                                                                                               |
|------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | F25T8SP35ECO                                                                                                                  |
| Manufacturer     | Ge By Current Lamps                                                                                                           |
| Description      | Ge Ecolux®, 25 WTT, 2080 LM, 3500 KV, 78 Cri, 1 In Diameter, 35.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life |
| Weight per unit  | 0.3500 (lbs/each)                                                                                                             |
| Product Category | Linear Fluorescent Straight La                                                                                                |

### Features

|              |                     |
|--------------|---------------------|
| average life | 30000.0             |
| Base         | Medium Bi-Pin (G13) |
| lumens       | 2080.0              |
| Wattage      | 25.0                |

### Material, Color, and Finish

|                             |        |
|-----------------------------|--------|
| color rendering index (cri) | 78.0   |
| color temperature           | 3500.0 |

### Dimensions and Weight

|          |       |
|----------|-------|
| Diameter | 1.0   |
| Length   | 35.78 |

### Descriptions

|                        |                                                                                                                               |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Description            | 25W T8 36" 3500K 78 CRI BI-PIN ENERGY SAVING                                                                                  |
| extra long description | GEL F25T8/SP35/ECO 45754 FLUORESCEN                                                                                           |
| Long Description       | GE Ecolux®, 25 WTT, 2080 LM, 3500 KV, 78 CRI, 1 IN Diameter, 35.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life |
| Product Type           | 45754 Fluorescent                                                                                                             |

### Manufacturer Information

|                           |                      |
|---------------------------|----------------------|
| Brand                     | Ge Traditional Lamps |
| GTIN                      | 00043168457545       |
| Manufacturers Part Number | F25T8/SP35/ECO       |
| UPC                       | 043168457545         |

### Taxonomies, Classifications, and Categories

|                      |             |
|----------------------|-------------|
| Category Description | Fluorescent |
|----------------------|-------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 24   |
| Weight Per each | 0.35 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....

Full Wattage .....