Product specifications

# Eaton CMBE4242B200BTS



## Catalog Number: CMBE4242B200BTS

Eaton Meter Breaker EUSERC ,Type CH EUCERC ,CSR2200N main breaker,Distribution section,200A, 120/240V, Ring, 42 spaces, 42 circuits, 22 kAIC,Surface mounting, Box size D, Al bus, OH/UG feed, 4-jaws, #6-250 kcmil line, #6-250 kcmil ground

## General specifications

| | |
|---|---|
| **Product Name** | **Catalog Number** |
| Eaton meter breaker EUSERC | CMBE4242B200BTS |
| **UPC** | **Product Length/Depth** |
| 782114869222 | 5.38 in |
| **Product Height** | **Product Width** |
| 34.38 in | 22 in |
| **Product Weight** | **Warranty** |
| 68 lb | Limited lifetime |
| **Compliances** | **Certifications** |
| EUSERC Approved | UL Listed |

Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Special features

Distribution section

### Type

All-in-ones

### Utility approvals

AZ : Arizona Public Service Company
AR : Entergy
LA : Entergy
MS : Entergy
TX : Entergy
ID : Idaho Power
OR : Idaho Power
WA : Seattle City Light
AK : Anchorage Municipal Light & Power
NV : NV Energy
AZ : Salt River Project (SRP)
CA : PacifiCorp/Pacific Power/Rocky Mountain Power
ID : PacifiCorp/Pacific Power/Rocky Mountain Power
OR : PacifiCorp/Pacific Power/Rocky Mountain Power
UT : PacifiCorp/Pacific Power/Rocky Mountain Power
WA : PacifiCorp/Pacific Power/Rocky Mountain Power
WY : PacifiCorp/Pacific Power/Rocky Mountain Power
MT : NorthWestern Energy
NE : NorthWestern Energy
SD : NorthWestern Energy
WY : NorthWestern Energy
AZ : Tucson Electric Power/ UniSource
AZ : Sulphur Springs Valley Electric Coop
WA : Puget Sound Energy
WA : Tacoma Public Utilities

### Interrupt rating

10 kAIC

### Box size

D

### Enclosure

NEMA 3R

### Ground

#6-250 kcmil

### Voltage rating

120/240 V

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER BREAKER PHOENIX STYLE

### Specifications and datasheets

Eaton Specification Sheet - CMBE4242B200BTS

Technical Data Residential Meter Breakers: Type CH and BR Residential

Number of sockets

1

Phase

Single-phase

Used with

Type CH breakers

Number of circuits

42

Bus material

Copper

Feed type

Top/bottom

Main circuit breaker

CSR2200N

Number of jaws

Four-jaw

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia