



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **IPLD3506 350MCM-#6 6 Pole Polaris Connector Block** *Nsi Industries*

Catalog Number	IPLD3506
Manufacturer	Nsi Industries
Description	The Polaris IPLD350-6 Multi-Tap Dual-Sided Entry Black Connector Features 6 Ports Sized For 350 MCM - 6 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable
Weight per unit	1.1 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Aluminum
Number of Conductors	6
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-6 AWG
Wire Type	Class B & C

### **Material, Color, and Finish**

Color	Black
Finish	Plastisol Insulated

### **Dimensions and Weight**

Size	L=6.670 - W=2.410 - H=2.610
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	350MCM-#6 6 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPLD350-6 POLARIS Ins Multi-Tap
Features	The Polaris IPLD350-6 6-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to six conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric stren
Long Description	The Polaris IPLD350-6 Multi-Tap Dual-Sided Entry Black Connector features 6 ports sized for 350 MCM - 6 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable
Product Type	Polaris Ins Multi-Tap 350 6 Port Dse
Special Features	(6) 350 MCM-6 AWG - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381924049
Manufacturers Part Number	IPLD350-6
UPC	662381924049

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Double Sided Entry

## Packaging

Carton	3
Weight Per each	1.1399

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C