

Description

The E4TATSB is a Non-IC Air-Tite™ housing optimized and listed for EISA compliant tungsten-halogen lamps, CFL and LED lamps, as well as incandescent. Housing features an adjustable socket bracket, and is suitable for residential or commercial applications. Installation in non-insulated ceilings with Air-Tite code compliant construction. If insulation is present it must be kept 3" from all sides of the housing. May be retrofit with compatible Halo LED lighting systems.

Catalog #		Type
Project		
Comments		Date
Prepared by		

Specification Features

Housing

- Die-formed CRS

Junction Box

- Seven conduit knockouts are uniform 1/2" size with true pry-out slots
- Compact galvanized steel junction box with xxin³ internal volume
- Listed for (10) #12 AWG 90°C splice conductors
- (7) 1/2" conduit pry-outs positioned to allow straight conduit runs
- (3) Slide-N-Side™ non-metallic (NM) wire traps allows wiring outside the box
- Accepts 14-2, 14-3, 12-2, 12-3 U.S. and 14-2, 14-3, 12-2 Canadian NM cable
- (3) 4-port push wire nuts with clear caps for quick and reliable mains voltage connections
- Three quick connect wire connectors included

Plaster Frame

- Housing is secured in plaster frame with spring barbs.
- The housing can be removed from the plaster frame to provide access to the junction box.
- Air-Tite gasket pre-installed on plaster frame.

Includes:

All Nail!™

- Integral precisely positioned nail for engineered and natural framing
- Mini-foot leveling flange
- Integral T-Grid Clip, no accessory clips required

Quick Connect™

- (3) Push wire nuts included, for speed & reliability
- Clear caps for wire connection visibility

Air-Tite™ code compliant

- ASTM E283 compliant

Socket

- Adjustable position bracket with porcelain socket and nickel plated brass screw shell provides flexibility in lamp positioning.

Thermal Protector

- Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation.

Trims

- Halo Fit-All concept offers multiple trim options in a variety of design styles, and functional beam distributions to control beam angle and lumen delivery in accommodating various lamp types.

Compliance

- cULus Listed 1598 Luminaire
- cULus Damp Location Listed
- cULus Listed for Wet Location, covered ceiling, with select trims
- RoHS Compliant
- Options to meet Trade Agreements Act requirements
- Air-Tite code compliant. Certified under ASTM E283; not exceeding 2.0 cfm (0.944 L/s) air leakage rate tested at a 1.57 psf (75 Pa) pressure differential



E4TATSB


**4" Non-Insulated Ceiling
AIR-TITE Recessed
Housing with Adjustable
Socket Bracket**

4" Trims



**FOR USE IN
NON-INSULATED CEILINGS
OR
INSULATED CEILINGS BUT
INSULATION MUST BE
KEPT 3" FROM ALL SIDES
OF FIXTURE**

Dimensions



Special Features

- All-Nail!™ bar hangers
- Quick Connect™ push wire nuts
- Air-Tite™ code compliant
- Slide-N-Side™ junction box

Ordering Information

Sample Number: E4TATSB 4003SC

Order housing, trim and lamp (by others) separately for a complete luminaire.

Domestic Preferences⁽¹⁾







[Blank] = Standard


TAA = Trade Agreements Act

Housing

E4TATSB = 4" AIR-TITE non-insulated ceiling small aperture housing with adjustable socket bracket

Trims

	<p>Reflectors</p> <p>999 Reflector Cone OD: 5-1/16" [129mm] 999P=Specular Clear, White Trim Ring 999RG=Residential Gold, White Trim Ring 999W=White Reflector, White Trim Ring 999H=Haze Reflector, White Trim Ring 999MB=Specular Black Reflector, White Trim Ring 999SN=Satin Nickel Reflector with Satin Nickel Trim Ring 999TBZ=Tuscan Bronze Reflector with Tuscan Bronze Trim Ring</p>
	<p>4003 Reflector Cone OD: 4-3/4" [120mm] 4003SC=Specular Clear Reflector, White Trim Ring</p>
	<p>Baffles</p> <p>953 Metal Baffle OD: 5-1/16" [129mm] 953P=Black Baffle with White Trim Ring 953W=White Baffle with White Trim Ring 953SN=Satin Nickel Baffle with Satin Nickel Trim Ring 953TBZ=Tuscan Bronze Baffle with Tuscan Bronze Trim Ring</p>
	<p>990 Pinhole Trim OD: 5-1/16" [129mm] 990P=White Die Cast Trim 990SN=Satin Nickel Die Cast Trim 990TBZ=Tuscan Bronze Die Cast Trim</p>
	<p>992 Wall Wash with Baffle OD: 5-1/16" [129mm] 992P=White Scoop and Trim Ring, Black Baffle 992W=White Scoop and Trim Ring, White Baffle 992SN=Satin Nickel Scoop and Trim Ring, Black Baffle 992TBZ=Tuscan Bronze Scoop and Trim Ring, Black Baffle</p>
	<p>993 Coilex Baffle OD: 5-1/16" [129mm] 993P=Black Baffle with White Trim Ring 993W=White Baffle with White Trim Ring 993SN=Black Baffle with Satin Nickel Trim Ring 993TBZ=Black baffle with Tuscan Bronze Trim Ring</p>

	<p>Baffles</p> <p>4001 Step Baffle OD: 4-3/4" [120mm] 4001BB=Black Plastic Baffle, White Trim Ring 4001WB=White Plastic Baffle, White Trim Ring</p>
	<p>4010 Metal Baffle OD: 5" [127mm] 4010BB=Black Metal Baffle, White Trim Ring 4010WB=White Metal Baffle, White Trim Ring</p>
	<p>Adjustable</p> <p>996 Eyeball 15° Tilt OD: 5-1/16" [129mm] 996P=White Eyeball 996SN=Satin Nickel Eyeball 996TBZ=Tuscan Bronze Eyeball</p>
	<p>998 Eyeball 30° Tilt OD: 5-1/16" [129mm] 998P=White Eyeball 998SN=Satin Nickel Eyeball 998TBZ=Tuscan Bronze Eyeball</p>
	<p>4002 Eyeball OD: 4-3/4" [120mm] 4002WH=White Eyeball</p>
	<p>Lens / Wet Location Listed</p> <p>945 Metropolitan Ice Light OD: 5-5/16" [135mm] 945=Clear Frosted 945Blue=Blue Frosted</p>
	<p>952 Cone Reflector 952PS=White Trim Ring, Dome Lens Shower Light</p>
	<p>4055 Prismatic Glass Lens Shower Light OD: 4-3/4" [120mm] 4055WH=Shower Light, White Trim Ring, Prismatic Flat Glass Lens</p>

Mounting Accessories

Filters and Lenses

The following filters and lenses can be substituted for the cover glass supplied for use with MR16 lamps.

Color Filters

L112=Red Gel Filter
L114=Ultraviolet Dichroic Filter
L120=Red Dichroic Filter
L121=Amber Dichroic Filter
L122=Yellow Dichroic Filter
L123=Green Dichroic Filter
L124=Daylight Blue Dichroic Filter
L125=Blue Dichroic Filter
L127=Cosmetic (2700°K) Dichroic Filter
L121=Yellow Gel Filter
L121=Amber Gel Filter

Optical Lenses

L100N=Diffuse Sand Blasted Lens. Provides an even beam spread from MR16 lamps- especially useful in wall washing.
L111=Soft Focus Lens. Smooths irregular beam pattern while maintaining high controlled illumination levels and beam angles.
L113=Prismatic Spread Lens. Provides a symmetrical broadening of MR16 lamp beams.
L115=Fans the MR16 beam to produce a wide rectangular illumination pattern.

Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to DOMESTIC.PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

*Outdoor rated lamp only (purchase separately)



For use in Halo listed housings.

Can also be used with the following LED Modules:

LT4 = 4" LED retrofit module

RL4 = 4" all-purpose retrofit LED retrofit module

RA4 = 4" adjustable gimbal all-purpose LED retrofit module

ML4 = 4" LED module (see ML4 spec sheets for trim options)

SLD4 = 4" surface LED downlight

SMD4 = 4" surface mount LED downlight