

Eaton 13100AQD03

Catalog Number: 13100AQD03

Eaton Photoelectric Sensor, Diffuse Reflective, Forward Viewing, Output ON, Dual key micro, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, 4 pin, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)

General specifications



Product Name	Catalog Number
Eaton Comet 18mm tubular photoelectric sensor	13100AQD03
	UPC
	782113843520
Product Length/Depth	Product Height
2.2 in	0.71 in
Product Width	Product Weight
0.47 in	0.2 lb
Warranty	Certifications
3 year	UL Recognized
	cUL Recognized

defaultTaxonomyAttributeLabel

Contact Rating

300 mA AC/DC at 20-264 Vac/15-30 Vdc

Enclosure material

Polyurethane foam (RIM)

Connection

Dual key micro

Contact configuration

DC: NPN open collector

AC: L1 switched

Sensor type

Diffuse reflective

Input voltage

20-264 Vac at 50/60 Hz, 15-30 Vdc (NPN)

LED indicator

Output ON

Number of pins

4

Protection

Latching short circuit

Maximum AC current

300 mA

Maximum DC current

300 mA

Operating temperature - max

158 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 4, NEMA 4X, NEMA 6, NEMA 12,
NEMA 13, IP69K

Resources

Brochures

[Comet series - Photoelectric sensors](#)

Catalogs

[Product Range Catalog Sensors – products, basic information, applications](#)

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - 13100AQD03](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)