



Atlanta, Georgia

Phone 800-521-7326

Fax 770-745-1333

Nylon Insert Lock Nut Zinc and Stainless





_				F		ŀ	1	ı	G
D			Width Across Flats			Thickness		Side Height	Width Across Corners
Peco	Basic Diameter		Basic	Min	Max	Min	Max	Ref	Ref
Catalog #	6	0.1380	5/16	0.305	0.313	0.168	0.188	0.103	0.339
	8	0.1640	11/32	0.336	0.345	0.219	0.239	0.140	0.374
	10	0.1900	3/8	0.367	0.376	0.229	0.249	0.140	0.410
See Section	1/4	0.2500	7/16	0.430	0.439	0.298	0.328	0.225	0.482
	5/16	0.3125	1/2	0.492	0.502	0.329	0.359	0.250	0.552
Four Of	3/8	0.3750	9/16	0.553	0.564	0.438	0.468	0.335	0.622
	7/16	0.4375	5/8	0.616	0.627	0.438	0.468	0.324	0.698
Our	1/2	0.5000	3/4	0.741	0.752	0.579	0.609	0.464	0.837
Catalog	9/16	0.5625	7/8	0.865	0.877	0.626	0.656	0.469	0.978
	5/8	0.6250	15/16	0.928	0.940	0.735	0.765	0.593	1.051
	3/4	0.7500	1-1/8	1.052	1.064	0.860	0.890	0.742	1.191
	7/8	0.8750	1-5/16	1.239	1.252	0.969	0.999	0.790	1.403
	1	1.0000	1-1/2	1.427	1.440	1.016	1.078	0.825	1.615

	Regular	Stainless			
Material	#2 - 5/8" - AISI 1008 - 1010 or equivalent steel; 3/4 - 1-1/2" AISI C1117 or equivalent steel	AISI 303 or equivalent steel			
Hardness	Rockwell C 28 maximum	1/4 - 5/8" - Rockwell B95 - C32; 34" - Rockwell B80 - C32			
Proof Load	90,000 psi	1/4 - 5/8" - 100,000 psi; 3/4" - 85,000 psi			

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.