



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



256RTI2 2-1/2" Raintight Diecast Compression Connector

Bridgeport Fittings

| | |
|------------------|--|
| Catalog Number | 256RTI2 |
| Manufacturer | Bridgeport Fittings |
| Description | 2-1/2" Raintight Insulated Connector, NPT Thread |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|----------------|------------------|
| Connector Type | Compression |
| insulation | Insulated Throat |
| Material | Zinc Die Cast |
| media | Yes |

Dimensions and Weight

| | |
|------|-------|
| Size | 2-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 2-1/2" RAIN TIGHT DIECAST COMPRESSION CONNECTOR |
| extra long description | BPT 256-RTI2 2-1/2" RAIN TIGHT INS |
| Features | Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations. |
| Long Description | 2-1/2" Raintight Insulated Connector, NPT THREAD |
| Product Type | 2-1/2" Rain Tight Ins Conn |
| Special Features | The Dual Internal sealing rings create a raintight seal. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747192561 |
| Manufacturers Part Number | 256-RTI2 |
| UPC | 781747192561 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | METALLIC FITTINGS |
| Type | Raintight Compression |

Trade Size

| | |
|------------|-------|
| Trade Size | 2-1/2 |
|------------|-------|

Packaging

| | |
|-----------------|--------|
| Carton | 12 |
| Weight Per each | 1.1916 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. With Bridgeport's newly redesigned Raintight Compression Connectors, 256-RTI2 thru 259-RTI2, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. These 2-1/2" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAIN TIGHT" clearly cast into the body.

standard

cULus

Temperature Rating

105°C