

INSTRUMENT / DEVICE ENCLOSURES



FEATURES-SPECIFICATIONS

Applications

Instrumentation housed in HK Series enclosures typically used to measure, detect, monitor, transmit and control industrial processes and systems.

HK Series enclosures are suitable for a broad range of applications, meeting both domestic and international code requirements.

Some specific examples of the type of instruments that can be housed in these enclosures include:

- Flow measurement devices
- Temperature monitors
- Two-wire transmitters
- Gas detectors
- Ph analyzers
- Pressure gauges
- Temperature transmitters
- Oxygen/combustible gas sensors
- Methane gas monitors
- Level detectors
- H2S monitors
- Transducers
- Pressure switches

See pages E57 - E58 for dimensions.

Features

- Enclosures are explosion proof, dust/ ignition proof, weather proof and tamper resistant
- HK Series boxes covers are cast from a copper-free aluminum alloy
- Cast stainless steel box, flat & lens cover available (HKSB-BC + HKSB-GLC)
- Neoprene 0-rings are provided with HK boxes to assure water resistance in NEMA 4/IP66 conditions
- Three box styles available: HKB, HKBD single cover design and the 2HKB double cover design. 2HKB enclosure has two separate chambers for isolation between



power and instrument.

- HKB, HKBD box has offset feed-thru conduit openings (3/4" NPT) for maximum use of interior volume
- 2HKB box has offset feed-thru conduit openings (3/4" NPT) on power side and one (3/4" NPT) on bottom instrument side
- Interior mounting pad for instrument/ device cast into the bottom of the HKB, HKBD box is provided in an "X"configuration for flexibility
- Location of the internal ground screw boss does not interfere with the mounting of the instrument or device
- Eight different cover styles are available: standard flat cover, standard glass lens cover, 1" dome cover, 1" dome lens cover, 2" dome cover, 2" glass lens dome cover, 4" dome cover and 4" dome lens cover.
- All covers have shrouded tamper resistant set screws as standard which can help to combat excessive vibration in rugged settings
- Lugs on cover permit easy removal and tightening

Material/Finish

- Boxes and covers copper-free aluminum (less than 4/10 of 1%)
- HKSB series is 316 cast stainless steel
- O-ring sealing gasket Neoprene rubber

ATEX/IECEx Certified

IECEX UL 14.0071U DEMKO 01 ATEX 15742U

Ex db IIC Gb, Ex tb IIIC Db IP66 Ta = -60°C to +70°C for GL (glass) lenses Ta = -60°C to +70°C for blank covers

Class I, Div. 1 & 2, Groups A*, B, C, D† Class I, Zones 1 & 2, Groups IIB + H2, IIA Class II, Div. 1 & 2, Groups E, F, G Class III, Type 3, 4, 4X



- File E83969 & File E150827






- Ground screws zinc plated steel with green dye (Stainless steel on HKSB)
- Allen head cover screw cadmium plated steel (Stainless steel on HKSB)
- Glass lens 3/8" thick tempered glass
- Finish silver powder epoxy paint, electrostatically applied
- Special colors available in quantity

- * Group A FM only on HK single cover box. Order with -GA suffix.
- ** CENELEC on assembled HK parts only with suffix "C".
- *** Seal immediately adjacent to enclosure
- † Seal within 18" of enclosure for Groups BCD and within 6" for Group A in accordance with sections 501-5 and 502-5 of the National Electrical Code.

HK Design Features



2HK Design Features







HK/2HK SERIES

INSTRUMENT / DEVICE ENCLOSURES

Boxes



HKBD







HKSB-GLC

Standard Flat Covers

















HFC Blank

HKGL Lens

HK1D Blank

HK1GLD Lens

HK2GLD Lens

HK4D Blank

HK4GLD Lens

FEATURES-SPECIFICATIONS

2HKB Series Boxes

The wall that separates the instrument side from the power side can be machined for slots or holes up to a maximum of two slots 5/16" by 1-1/2".

Submit drawings for machining requirements to Killark.

Factory Modifications

Approvals allow for factory or field modifications on HKB box for drilling and tapping conduit openings on side or back of enclosure without voiding UL-CSA-FM approvals. Internal mounting pad holes on "X" configured boss can be factory added by drilling from inside of box without piercing the bottom of enclosures. Assemblies with ATEX/IEC Ex approvals must be factory modified in order to comply with certifications.

HK ASSEMBLED PARTS@3							
CATALOG NUMBER (CAST ALUMINUM)							
HKB BOX & COVERS		HKBD BOX & COVERS	2HKB BOX W / BLANK COVER ON POWER SIDE & OPTIONAL COVER ON INSTRUMENT SIDE		COVER		
UL-CSA-FM APPROVED	CENELEC UL-CSA-FM APPROVED	UL-CSA-FM Approved	(UL-CSA-FM)	CENELEC UL-CSA-FM APPROVED®	TYPE		
HKB-B	HKB-BC	HKBD-B	2HKB-B-B	2HKB-BC-BC	Standard flat		
HKB-2D	HKB-2DC	HKBD-2D	2HKB-B-2D	2HKB-BC-2DC	2" Dome		
HKB-4D	HKB-4DC	HKBD-4D	2HKB-B-4D	2HKB-BC-4DC	4" Dome		
HKB-GL	HKB-GLC	HKBD-GL	2HKB-B-GL	2HKB-BC-GLC	Lens		
HKB-2GLD	HKB-2GLDC	HKBD-2GLD	2HKB-B-2GLD	2HKB-BC-2GLDC	2" Dome lens		

HK COMPONENT PARTS				
CATALOG NUMBER	DESCRIPTION			
НКВ	Single cover box only			
HKBD	Single deep box only			
2HKB	Double cover Box only			
HFC	Flat cover			
HKGL	Lens cover			
HK1D	1" Dome cover			
HK1GLD	1" Dome lens cover			
HK2D	2" Dome cover			
HK4D	4" Dome cover			
HK2GLD	2" Dome lens cover			
HK4GLD ©	4" Dome lens cover			
15722LABB	Rep. "O" Ring Gasket			

HKSB STAINLESS STEEL ASSEMBLED PARTS②			
HKSB BOX & COVERS CENELEC UL-CSA-FM APPROVED	COVER TYPE		
HKSB-BC	Standard flat		
HKSB-GLC	Lens		

- ① Assemblies that are CENELEC approved include as standard:
 - · External ground screw with terminal
- · Predrilled nameplate holes and screw on pad for customer installed nameplate.
- ② See information at right for optional factory machining. 3 Product is stocked at component level. Recommend
- ordering as such for reduced lead time. 2HKB Assemblies include a flat cover on power side, dome and lens covers can be substituted in place of flat cover, consult factory for ordering details.
- S Not FM Approved

HKB FACTORY MODIFICATIONS					
OPTIONAL FACTORY MACHINING (HKB)					
CATALOG SUFFIX	DESCRIPTION				
-01 -	1/2 NPT hub in back				
-02 -	3/4 NPT hub in back				
-10 -	1/2 NPT hub in side				
-20 -	3/4 NPT hub in side				
-21 -	3/4 NPT hub in side 1/2 NPT hub in back				
-22 -	3/4 NPT hub in side 3/4 NPT hub in back				
-028 -	3/4 NPSM hub in back				
-22\$ -	3/4 NPT hub in side 3/4 NPSM hub in back				
-2\$2\$ -	3/4 NPSM hub in side 3/4 NPSM hub in back				
-280 -	3/4 NPSM hub in side				
-2\$1 -	3/4 NPSM hub in side 1/2 NPT hub in back				
-282 -	3/4 NPSM hub in side 3/4 NPT hub in back				
-GS	External ground screw (Standard on HKB assembly with CENELEC approvals)				
-GA -	Group A - FM approval (Available only on HKB box furnished with covers installed)				
-SU93 -	Unpainted - Natural finish				
-SU9 -	Special colors of powder paint available in quantity. Consult factory for details				
011					

Ordering examples: Modified box component HKB-20 Modified assembly HKB - B - 20 OR HKB - BC - 20



INSTRUMENT / DEVICE ENCLOSURES







HKSB - Stainless Steel

FEATURES-SPECIFICATIONS

Dimensions Note: Add 1/2" to all depth dimensions when using HKBD Deep Box. HKBD volume = 33 cu.in.





HKB Volume: 31 cu. in.



TURNING RADIUS 2²¹/₃₂" (67) TYPICAL ALL COVERS 2¹³/₁₆" (71) INSIDE 37/g (98) O.A. Щ 1/2"(13) TYP. /₁₆"(8) TYP. Flat Cover


HKB box and blank cover






For HK1GLD (1" Dome Lens Cover), add 1" to lens cover verticle height dimensions

For HK4GLD (4" Dome Lens Cover), add 2" to 2 dome lens cover verticle height dimensions





2HK SERIES


INSTRUMENT / DEVICE ENCLOSURES





2HK

FEATURES-SPECIFICATIONS


Dimensions













2 HKB BOX w/HK4D 4" LENS/DOME COVER & HFC BLANK COVER



2 HKB BOX w/HKGL LENS/DOME COVER & HFC BLANK COVER



2 HKB BOX w/HK2D 2" DOME COVER & HFC BLANK COVER

