

301 Commerce Suite 2700 Fort Worth, Texas 76102 817-215-7000 817-215-7001 (Fax)

TECHNICAL SPECIFICATION

Electrical Nonmetallic Tubing (ENT) Fittings Threaded Terminal Adapter

SCOPE

This specification covers the requirements for Electrical Nonmetallic Tubing Threaded Terminal Adapters in trade sizes ½" to 2", for use with Royal Pipe Systems ENT. These fittings are certified to the Canadian Standards Association (CSA) standard C22.2 227.1/Underwriters Laboratories (UL) Standard 1653, including concrete tightness requirements.

MARKING


ENT Threaded Terminal Adapter markings are as specified in CSA C22.2 No. 227.1/UL 1653.

TEST REQUIREMENTS

Quality testing is as per Royal's Quality Assurance program and in accordance with CSA C22.2 No. 227.1/UL1653.

THREADED TERMINAL ADAPTER DIMENSIONS

| Trade Size | A (in) | B (in) | C (in) | D (in) |
|------------|--------|-------------------|--------|--------|
| 1/2" | 1.620 | ½" – 14 NPT | 0.600 | 1.235 |
| 3/," | 1.548 | 3/4" – 14 NPT | 0.797 | 1.529 |
| 1" | 1.763 | 1" – 11-1/2 NPT | 1.010 | 1.793 |
| 1 ¼" | 2.011 | 1 ¼" – 11-1/2 NPT | 1.375 | 2.239 |
| 1 ½" | 2.031 | 1 ½" – 11-1/2 NPT | 1.605 | 2.463 |
| 2" | 2.178 | 2" – 11-1/2 NPT | 2.063 | 2.963 |



Prepared: March 30, 2007

By: S. Scott

Revised: December, 2010-Add new ENT fitting information