



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 36241012 Encl 10X24X36 N12 CH CLMP CVR

*Cooper B-Line/Cable Tray*

Catalog Number	36241012
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 10" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	67.6 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

dimensions	10.0000 IN X 24.0000 IN X 36.0000 IN
Material	Carbon Steel
Mounting Type	Wall

### Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

### Dimensions and Weight

Size	24.00 In Width X 10.00 In Depth X 36.00 In Height
------	---

### Descriptions

Description	ENCL 10X24X36 N12 CH CLMP CVR
extra long description	B-LINE 362410-12 TYPE 12 SGL-DOOR E
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 36" height, 10" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 36X24X10
Special Features	Plated door clamps

### Manufacturer Information

Brand	Eaton
GTIN	00782051803501
Manufacturers Part Number	362410-12
UPC	782051803501

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	67.59

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and ControlsDatacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures - Safety and Security SystemsCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional Buildings / Structures - Critical PowerUtility - Substations, Utility Transmission and DistributionCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Stru
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	CSA C22.2.,NEMA,UL 508A