

# Eaton 7501B-BOX

Catalog Number: 7501B-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Brown, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 752391



## Product specifications

### Special features

Box

### Phase

Single-phase

### Closure type

Maintained

### Wiring method

Back and push

### Mounting method

Flush

### Amperage Rating

15A

### Type

Switch decorator

### Switch type

Single-pole

### Load type

Motor Control

ELV

LED

Fan

CFL

HAL

MLV

FLR

INC

### Color

Brown

### Material

Thermoplastic

### Allowable wire size

#14-12 AWG

### Number Of Poles

Single-pole

### Voltage rating

120/277 V

[Actuator](#)

[Decorator](#)

[Resources](#)

[Brochures](#)

[Decorator standard grade switches spec sheet](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - 7501B-BOX](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)