

Specifications



Eaton ABC-20-R

Eaton MDQ Series Dual-element, Time-delay fuse, 10A, 32 Vac, 10

General specifications

PRODUCT NAME	Eaton Bussmann series ABC fast-acting fuse
CATALOG NUMBER	ABC-20-R
UPC	051712646222
EAN	5027590226479
PRODUCT HEIGHT	32 mm
PRODUCT DIAMETER	6.4 mm
PRODUCT WEIGHT	2.8 g
COMPLIANCES	CE Marked RoHS Compliant
CATALOG NOTES	Ceramic body allows for higher amp/volt rating combinations.

Product specifications

AMPERAGE RATING	20 A
MELTING (I ₂ T)	Typical pre-arc: 550.8
RESISTANCE	0.00366 ohms DC cold
VOLTAGE DROP	0.1 mV typical
INTERRUPT RATING	10 kAIC at 125 Vdc 1 kAIC at 125 Vac 400 AIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	4 hr at 100%, 60 min at 135%, 120 sec at 200%
MATERIAL	Nickel-plated brass endcaps Ceramic tube
QUANTITY	5
VOLTAGE RATING	250 Vac, 125 Vdc, 32 Vac (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

PEP ECO-PASSPORT [EATO-00033-V01.01-EN](#)

SPECIFICATIONS AND DATASHEETS [Eaton ABC fast-acting ceramic tube fuses data sheet](#)

[Eaton Specification Sheet - ABC-20-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

