

Project:

Type:

Prepared By:

Date:



UPC: 019813750477

Features and Benefits

- Energy efficient replacement for incandescent and halogen reflector lamps
- Constructed from durable plastic which lowers risk of breakage
- Rated for use in enclosed and open fixtures in dry or damp locations
- Frosted lens produces smooth diffuse light
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- ENERGY STAR Compliant
- Dimmable with common dimmer types (see Dimmer Compatibility List)

Technical Specifications

Performance

Product Type:  
Reflector

Input Wattage:  
13W

Lumens:  
950lm

Efficacy:  
73lm/W

L70 Lifespan:  
25,000-Hour LED lifespan based on IES LM-70 results

Wattage Equivalency:  
75W

LED Characteristics

Color Accuracy (CRI):  
80

Color Temperature:  
3000K

Electrical

Power Factor:  
>0.9

Dimmable:  
Yes, down to 20%

Input Voltage:  
120V

Operating Temperature:  
-20°C to 40°C

Construction

Bulb Shape:  
BR40

Enclosure Material:  
Plastic

Housing Finish:  
White

Lens Finish:  
Frosted

Base Type:

E26 Edison

Optical

Beam Angle:  
110°

Other

Technology EQ:  
Incandescent

Compliance

UL Listed:  
Yes

Environment:  
Damp / Enclosed

Energy Star ID:  
2329453

Rohs:  
Mercury and UV free. RoHS-compliant components.

FCC:  
Complies with Part 15B of the FCC Rules


Technical Specifications (continued)

Certification Model Number:  
BR40-13-830-DIM


Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	6	15.8	10.6	7
PALLET	360	47.2	37	34.8

Dimension



Light Distribution



Project:

Type:

Prepared By:

Date:



UPC: 019813750477

Features and Benefits

- Energy efficient replacement for incandescent and halogen reflector lamps
- Constructed from durable plastic which lowers risk of breakage
- Rated for use in enclosed and open fixtures in dry or damp locations
- Frosted lens produces smooth diffuse light
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- ENERGY STAR Compliant
- Dimmable with common dimmer types (see Dimmer Compatibility List)

Technical Specifications

Performance

Product Type:  
Reflector

Input Wattage:  
13W

Lumens:  
950lm

Efficacy:  
73lm/W

L70 Lifespan:  
25,000-Hour LED lifespan based on IES LM-70 results

Wattage Equivalency:  
75W

LED Characteristics

Color Accuracy (CRI):  
80

Color Temperature:  
3000K

Electrical

Power Factor:  
>0.9

Dimmable:  
Yes, down to 20%

Input Voltage:  
120V

Operating Temperature:  
-20°C to 40°C

Construction

Bulb Shape:  
BR40

Enclosure Material:  
Plastic

Housing Finish:  
White

Lens Finish:  
Frosted

Base Type:

E26 Edison

Optical

Beam Angle:  
110°

Other

Technology EQ:  
Incandescent

Compliance

UL Listed:  
Yes

Environment:  
Damp / Enclosed

Energy Star ID:  
2329453

Rohs:  
Mercury and UV free. RoHS-compliant components.

FCC:  
Complies with Part 15B of the FCC Rules


Technical Specifications (continued)

Certification Model Number:  
BR40-13-830-DIM

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	6	15.8	10.6	7
PALLET	360	47.2	37	34.8

Dimension



Light Distribution

