



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BRNSURGE Type BR 2 Pole Surge Arrester *Eaton Corp*

Catalog Number	BRNSURGE
Manufacturer	Eaton Corp
Description	Eaton Type BR Circuit Breaker Surge Protective Device, Two Pole, Surge Protective Device
Weight per unit	1.0 (lbs/each)
Product Category	Distribution Equipment

### Features

dimensions	3.6000 IN X 3.5000 IN X 2.2500 IN
Short Circuit Rating	10 kA

### Dimensions and Weight

Depth	3.6000
Height	2.2500
Width	3.5000

### Descriptions

Description	TYPE BR 2 POLE SURGE ARRESTER
extra long description	ETN BRNSURGE Type BR 2 pole Surge A
Features	Eaton offers a comprehensive family of surge products for use at service entrances. These products can help protect sensitive electronics against the damaging effects of surges. Due to the evolution of electronics and microprocessors in the home, there is a continuous challenge to provide quality (clean) power for electronic loads such as appliances, computers/home office and entertainment systems. Surges caused by lightning, utility grid switching and other sources travel on current carrying conductors t
Long Description	Eaton Type BR circuit breaker surge protective device, Two Pole, Surge Protective Device
Product Type	Type BR 2 Pole Surge Arrester

### Manufacturer Information

Brand	Eaton
GTIN	00786689353667
Manufacturers Part Number	BRNSURGE
UPC	786689353667

### Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	Plug on module surge protection device



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1

## Uses, Certifications, and Standards

Application	OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Frequency Rating	50/60 Hz
standard	cUL Certified,UL 1449