



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BVT050SS4 BLTD 1/2" SS Vibra-Clamp/Strut Strap

Cooper B-Line/Cable Tray

Catalog Number	BVT050SS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Vibra-Clamp Vibration and Cushion Clamp, 1.49" H X 0.74" L X 1.25" W, Steel, 400 LBS Load Cap
Weight per unit	0.1536 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	0.7400 IN X 1.2500 IN X 1.4900 IN
Material	304 Stainless Steel

Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 304
--------	--------------------------

Dimensions and Weight

Size	1/2 In (OD), 3/8 In (Copper Tube)
------	-----------------------------------

Descriptions

Construction	TWO PIECE
Description	BLTD 1/2" SS VIBRA-CLAMP/STRUT STRAP
extra long description	B-LINE BVT050SS4 VIBRACLAMP, COPPER
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series Vibra-Clamp vibration and cushion clamp, 1.49" H x 0.74" L x 1.25" W, Steel, 400 Lbs load cap
Product Type	Vibraclamp, Copper & Od, 1/2", SSL 304
Special Features	Includes Cushion, Clamp, Screw and Nut, Dielectric Strength 400 Volts/Mil, 0.74 In Width X 1.49 In Height

Manufacturer Information

Brand	Eaton
GTIN	00781011028015
Manufacturers Part Number	BVT050SS4
UPC	781011028015

Taxonomies, Classifications, and Categories

Category Description	CONDUIT HANGERS/STAND OFF STRAPS
Type	Vibration and cushion clamp

Packaging

Carton	1
Weight Per each	0.1536



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable
Temperature Rating	-40 To 300 Deg F