Specifications



Photo is representative





Eaton C0500E6U

Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, cu magnet wire, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°c, 500 va

General specifications	
PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0500E6U
UPC	786680019159
PRODUCT LENGTH/DEPTH	7.008 in
PRODUCT HEIGHT	4.449 in
PRODUCT WIDTH	5.236 in
PRODUCT WEIGHT	25.6 lb
WARRANTY	Eaton Selling Policy 25- 000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified cUL Certified UL Listed
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
PRODUCT TYPE	Industrial control transformer



Physical Attributes	
COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings	
PRIMARY VOLTAGE	208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	500 VA
SECONDARY VOLTAGE	99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources	
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet - C0500E6U</u>

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

 $\hbox{@ 2025 Eaton.}$ All Rights Reserved.

Follow us on social media to get the latest product and support information.











Specifications



Photo is representative





Eaton C0500E6U

Eaton Type MTE industrial control transformer, pv: 240/416/480/600v, 230/400/460/575v, 220/380/440/550v, 208/500v, cu magnet wire, taps: none, sv: 99/120/130v, 95/115/125v, 91/110/120v, 85/100/110v, 55°c, 500 va

General specifications	
PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0500E6U
UPC	786680019159
PRODUCT LENGTH/DEPTH	7.008 in
PRODUCT HEIGHT	4.449 in
PRODUCT WIDTH	5.236 in
PRODUCT WEIGHT	25.6 lb
WARRANTY	Eaton Selling Policy 25- 000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified cUL Certified UL Listed
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
PRODUCT TYPE	Industrial control transformer



Physical Attributes	
COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Performance Ratings	
PRIMARY VOLTAGE	208/500 V, 220/380/440/550 V, 230/400/460/575 V, 240/416/480/600 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	500 VA
SECONDARY VOLTAGE	99/120/130 V, 95/115/125 V, 91/110/120 V, 85/100/110 V

Resources	
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet - C0500E6U</u>

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

 $\hbox{@ 2025 Eaton.}$ All Rights Reserved.

Follow us on social media to get the latest product and support information.









