



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **CGB397SA 1 NPT Male Al Cord/Cab FTG Neo Bush** *Crouse-Hinds*

Catalog Number	CGB397SA
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CGB Cable Gland, Cable Range Min/Max: 0.750-0.875", Non-Armoured and Tray Cable, Non-Armoured, Aluminum, General Purpose, 1" NPT
Weight per unit	0.2200 (lbs/each)
Product Category	Cable & Cord Grips

### **Features**

connection	Male NPT
dimensions	2.3800 IN X 1.6600 IN X 1.6600 IN

### **Descriptions**

Description	1 NPT MALE AL CORD/CAB FTG NEO BUSH
extra long description	CRS-H CGB397 SA 1 NPT MALE AL CORD/
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round
Long Description	Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.750-0.875", Non-armoured and tray cable, Non-armoured, Aluminum, General purpose, 1" NPT
Product Type	1 NPT Male Al Cord/Cab FTG Neo Bush
Special Features	Non-Armored Gland

### **Manufacturer Information**

Brand	Eaton
GTIN	00782274100852
Manufacturers Part Number	CGB397 SA
UPC	782274100852

### **Taxonomies, Classifications, and Categories**

Category Description	MISC FITTINGS
Type	Cable gland



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.22

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 2
standard	UL (CANADA AND US)
Temperature Rating	-25 To 40 Deg C