



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GAR1829 250MCM Ground Conn *Burndy LLC*

Catalog Number	GAR1829
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 Awg (Sol) -250 Kcmil, 2" Pipe, 2"-2-3/8"Rod, Bright Dipped.
Weight per unit	1.7 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Bolt Size	3/8
Material	Copper

Material, Color, and Finish

Finish	Dip Coat-Primed/Powder-Coated/Textured Paint
--------	--

Descriptions

Description	250MCM GROUND CONN
extra long description	BUR GAR1829 2/0-250CU 2IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 2" Pipe, 2"-2-3/8"Rod, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 2 - 2-3/8 IN, Tube (ips) Size: 2 IN, Height: 4-1/2 IN, Width: 3-3/4 IN, Installation Torque: 240 IN-LB

Manufacturer Information

Brand	Burndy Canada
GTIN	00781810235201
Manufacturers Part Number	GAR1829
sub brand	DURIMUM
UPC	781810235201

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GAR



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.67

Uses, Certifications, and Standards

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
standard	UL467