

# Eaton CHP22B100X2

Catalog Number: CHP22B100X2

Eaton CH main breaker loadcenters, PON, Main breaker, 100 A, X2, Copper, X2, NEMA 1, Metallic, 10 kAIC, CH, 44, 22, Three-wire, Single-phase, #6-1/0 AWG, 120/240 V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP22B100X2
UPC	Product Length/Depth
786679189559	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
12.3 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Purchase Size X2 Cover Separately
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

100 A

### Bus material

Copper

### Cover

X2

### Main circuit breaker

CH

### Number of circuits

44

### Number of spaces

22

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X2

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP22B100X2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHP22B100X2

Catalog Number: CHP22B100X2

Eaton CH main breaker loadcenters, PON, Main breaker, 100 A, X2, Copper, X2, NEMA 1, Metallic, 10 kAIC, CH, 44, 22, Three-wire, Single-phase, #6-1/0 AWG, 120/240 V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP22B100X2
UPC	Product Length/Depth
786679189559	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
12.3 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Purchase Size X2 Cover Separately
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

100 A

### Bus material

Copper

### Cover

X2

### Main circuit breaker

CH

### Number of circuits

44

### Number of spaces

22

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X2

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP22B100X2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)