



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHP32N225X6 CH Pon Loadctr 225A Convertible 32 Spaces

Eaton Corp

Catalog Number	CHP32N225X6
Manufacturer	Eaton Corp
Description	Eaton CH Plug-On Neutral Loadcenter, 225A, Convertible, 32 Spaces
Weight per unit	18.9 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

amperage rating	225
Cover Type	X6
dimensions	34.1200 IN X 14.3100 IN X 3.8800 IN
interrupt rating	25
media	Yes
number of spaces	32
Phase	1
Voltage Rating	120/240 V
Wattage	Single-pole

### Dimensions and Weight

Depth	34.1200
Height	3.8800
Size	X6
Width	14.3100

### Descriptions

Description	CH PON LOADCNTR 225A CONVERTIBLE 32 SPACES
extra long description	ETN CHP32N225X6 CH PON LC, 225A, CO
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH plug-on neutral loadcenter, 225A, convertible, 32 spaces
Product Type	CH Pon LC, 225A, Conv, 32SP



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Eaton
GTIN	00786689055196
Manufacturers Part Number	CHP32N225X6
UPC	786689055196

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Convertible loadcenter

## Packaging

Carton	1
Weight Per each	18.9

## Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 67,UL 50