



SKU: CLND-250-38-1

UPC: 0783669641349

Features & Benefits:

Description: Surecrimp Copper Compression Lug, Conductor Size 250, 2 Holes, 3/8in Bolt Size, 1in Hole Spacing, Long Barrel, No Sight Window, Tin Plated, UL, CSA

Specs

Additional Class Attributes

Barrel Marking	Ink
Barrel Type	Long
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	No
Flared End	No
ILSCOs Die Catalog Number	ILD-62
ILSCOs Die Index Number	I-62
Mounting Hole Type	Thru
Narrow Tang	No
Number of Mounting Holes	2
Sight Window	No
Slotted	No
Tang End Shape	Square
Undrilled	No

Dimensions

Barrel Length (IN)	1.688
Barrel Length (mm)	42.8752
Dimension G (IN)	0.414
Dimension G (mm)	10.5156
Height (IN)	0.79
Height BX (IN)	2
Height (mm)	20.066
Inside Diameter (IN)	0.593
Inside Diameter (mm)	15.0622
Length (IN)	4.156
Length (mm)	105.5624
Mounting Hole Diameter (IN)	0.406
Mounting Hole Diameter (mm)	10.3124
Mounting Hole Spacing (IN)	1
Mounting Hole Spacing (mm)	25.4
Outside Diameter (IN)	0.75
Outside Diameter (mm)	19.05
Strip Length (mm)	44.45
Tang Length (IN)	1.937
Tang Length (mm)	49.1998
Tang Thickness (IN)	0.157
Tang Thickness (mm)	3.9878

Tang Width (IN)	1.088
Tang Width (mm)	27.6352
Weight (LB)	0.206923613995703
Weight BX (LB)	2.298
Width (IN)	1.088
Width BX (IN)	6.1875
Width (mm)	27.6352

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	250 kcmil
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	250 kcmil - 1/0 Str
Flex Conductor Range	4/0 G,H,I,K,M,DLO

Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA
Material	Copper

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Direct Burial	Yes
Dual Rated	No
NEMA Code	S-588-3
UPC Code	78366964134

Bolt and Screw Sizes

Mounting Bolt/Stud Size	3/8
-------------------------	-----

Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
NEBS Rating	Level 3
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

Environment and Temperature

Temperature Rating

90°C

Color

Color

Silver

Color Code

Yellow

Voltage

Voltage Rating

35 kV