

ELLIOTT ELECTRIC SUPPLY 1201 West Broadway 79714-0000, TX Andrews Phone: 432-523-2423 Four 422-523-2428

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 432-523-2428



GHC2020 Type GHC BRKR 2P 20A 277/480VAC Max 125/250VDC Max Eaton Corp

66	
Catalog Number	GHC2020
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHC, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 20A, 480Y/277 Vac, 125/250 VDC, 65 Kaic At 240 Vac, 14 Kaic At 480Y/277 Vac, 50/60 HZ
Weight per unit	
Product Category	2 Dolo
Features	
Current Rating	20 A
dimensions	2.6300 IN X 2.0000 IN X 4.8800 IN
frame	
media	Vos
Poles	2
Voltage Rating	480Y/277 Vac, 125/250 Vdc
Descriptions	
Description extra long description	TYPE GHC BRKR 2P 20A 277/480VAC MAX 125/250VDC MAX ETN GHC2020 GHC CB 2P 20A 277/480VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHC, Complete breaker, Fixed thermal, fixed magnetic trip type, Two-pole, 20A, 480Y/277 Vac, 125/250 Vdc, 65 kAIC at 240 Vac, 14 kAIC at 480Y/277 Vac, 50/60 Hz
Product Type	GHC CB 2P 20A 277/480VAC Max 125/250VDC
Manufacturer Information	
Brand	Eaton
GTIN	00786679174081
Manufacturers Part Number	GHC2020
UPC	786679174081



standard

ELLIOTT ELECTRIC SUPPLY 1201 West Broadway 79714-0000, TX Andrews Phone: 432-523-2423 Fax: 432-523-2428

Taxonomies, Classifications, and Cat	egories
	MOLDED CASE BREAKERS
Туре	Molded case circuit breaker
Packaging	
Carton	1
Package	12
Weight Per each	1.1
Uses, Certifications, and Standards	
Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and FOEMs - Other

UL Listed