



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **E59M30C129A01A1 30MM Iprox Clone Ac Uns 29MM SN No Micro** *Eaton Corp*

Catalog Number	E59M30C129A01A1
Manufacturer	Eaton Corp
Description	Eaton Iprox Sensor, E59, Straight, 30 MM, Unshielded, 360° Viewable Led, Dual Key Micro, 200 Ma At 20-132 V, 3 Pin, <3% Sensing Range, 2-Wire Ac, No, 20-132V
Weight per unit	0.3000 (lbs/each)
Product Category	Inductive Proximity Sensor

### **Features**

Accuracy	< 3% sensing range
connection	Dual key micro
dimensions	2.9200 IN X 1.1800 IN X 1.1800 IN
media	Yes

### **Dimensions and Weight**

Depth	1.18110
Size	30 MM

### **Descriptions**

Description	30MM IPROX CLONE AC UNS 29MM SN NO MICRO
extra long description	ETN E59-M30C129A01-A1 30MM IPROX CL
Features	These unique, adaptable, field-programmable sensors utilize exclusive SmartSense technology—featuring an embedded microprocessor—to perform special sensing functions at extended ranges. These capabilities include programmable attributes, such as sensing range, output types, contact types, response time and noise immunity. No other sensor on the market offers such extensive programmability.
Long Description	Eaton iProx Sensor, E59, Straight, 30 mm, Unshielded, 360° viewable LED, Dual key micro, 200 mA at 20-132 V, 3 pin, <3% sensing range, 2-wire AC, NO, 20-132V
Product Type	30MM Iprox Clone, Ac, Uns 29MM SN, No Micro

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00782116183715
Manufacturers Part Number	E59-M30C129A01-A1
UPC	782116183715

### **Taxonomies, Classifications, and Categories**

Category Description	SENSORS
Type	Programmable inductive proximity sensor



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Stationary Mach Equip In Factory - Other Stationary Machinery and Equipment - In Factory
environmental conditions	NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67, IP69K
standard	UL Listed, CSA Certified, CE Marked
Temperature Rating	-40 to 158 °F