



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EL59 1-1/2" 90D Female Cond Elbow *Crouse-Hinds*

Catalog Number	EL59
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series EL Elbow, Female, Feraloy Iron Alloy or Ductile Iron, 90°, 1-1/2"
Weight per unit	2.9 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Female Threaded
dimensions	5.2200 IN X 2.4400 IN X 5.2200 IN

Descriptions

Description	1-1/2" 90D FEMALE COND ELBOW
extra long description	CRS-H EL59 1-1/2 NPT IRON 90 DEG FE
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit
Long Description	Eaton Crouse-Hinds series EL elbow, Female, Feraloy iron alloy or ductile iron, 90°, 1-1/2"
Product Type	1-1/2 NPT Iron 90 Deg Female Div 1 Elbow

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274307602
Manufacturers Part Number	EL59
UPC	782274307602

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	ELBOW

Packaging

Carton	1
Package	2
Weight Per each	2.85



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II
	Div 2 Group F G, Class III
standard	UL 886, CSA C22.2