



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICN3P32N35M 120-277V Elec Bal

Advance By Signify

Catalog Number	ICN3P32N35M
Manufacturer	Advance By Signify
Description	Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology.
Weight per unit	0.8600 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	0.71-0.31
ANSI Code	N/A
Ballast Factor	0.88
dimnable	Non Dimmable
Lamp Type	Fluorescent
Minimum Starting Temperature	-20
Number of Lamps	3
Power Factor	0.98
start type	Instant
total harmonic distortion	<=10
Voltage Rating	120-277
Wattage	87-85

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Height	3.94
Length	3.74
Width	5.12

Descriptions

Description	120-277V ELEC BAL
extra long description	ADV 109116 ELE BALLAST (3) F32T8 12
Long Description	Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.
Product Type	Ele Ballast (3) F32T8 120-277V
Special Features	IntelliVolt 120-277V, Parallel Lamp Operation



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Advance
GTIN	00781087091500
Manufacturers Part Number	109116
UPC	781087091500

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	ELECTRONIC

Packaging

Carton	1
Weight Per each	0.86

Uses, Certifications, and Standards

Application	Commercial
Frequency Rating	50to60
Mounting standard	8.9 CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;NOM certificate;RoHS Compliant