

BORESCOPE

ET510

The Klein Tools Video Borescope is used to view inaccessible areas. It features a durable camera snake with an adjustable work light.



For Professionals...Since 1857®

KLEIN TOOLS®



Actual image



Multiple Applications!

- Electrical • HVAC • Plumbing
- Automotive • Aircraft

GENERAL SPECIFICATIONS:

Screen Size:	2.4" (61 mm)
Screen Resolution:	480 x 234 px
Color Depth:	24 bits
Fixed Focus Distance:	1.97"~5.90" (5~15 cm)
Camera Diameter:	0.67" (17 mm)
Gooseneck Length:	3.28' (1 m)
Maximum Length:	9.84' (3 m)
Battery Specification:	Lithium Ion 3.7V 2000mAh

Features

- Waterproof / Dustproof Camera (IP67)
- Adjustable LED Worklight • High Resolution Screen
- Mirror Image

Included Accessories

- Main Unit
- Gooseneck Camera 17 mm
- 3.7V 2000mAh Rechargeable Li-Ion Battery
- Mirror Camera Attachment
- Hook Camera Attachment
- Magnet Camera Attachment
- USB Power Adapter/Charger
- Instruction Manual



ET510

Additional Accessories Available

Accessories	Description
69454	Camera Replacement
69455	Camera Extension
69457	Camera Attachments

Cat. No.	Batteries	Height	Width	Depth	Weight (Main Unit)
ET510	Lithium Ion	6.53" (16.59 cm)	2.84" (7.22 cm)	1.55" (3.95 cm)	8.08 oz (229.3 g)

All dimensions are in inches and (millimeters) unless otherwise specified.

⚠ WARNING: The Borescope and gooseneck camera are NOT insulated. Avoid probing areas where energized conductive elements may be present. Shut off power to the nearby work areas before starting work. Avoid probing areas where chemicals may be present. Do not probe moving machinery that could catch the Borescope and cause harm to the operator and the Borescope. The Borescope is not intended for use on people or animals. Do not use the Borescope near sources of heat. Keep steady footing at all times, following ladder safety procedures when necessary. Do not use if the Borescope casing is cracked or broken in any way.

