



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1722 Primewest Parkway  
77449-0000, TX Katy  
Phone: 281-828-2012  
Fax: 281-828-2512



## IPLD5004 500MCM-#4 4 Pole Polaris Connector Block

*Nsi Industries*

Catalog Number	IPLD5004
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #4 Awg Conductor Size, 500 MCM Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 4 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 5.24 In Overall Length, 600 V, 1.0499 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	500 MCM-4 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=5.240 - W=2.830 - H=2.910
------	-----------------------------

### Descriptions

Description	500MCM-#4 4 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPLD500-4 POLARIS Ins Multi-Tap
Features	The Polaris IPLD500-4 4-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to four conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 500 MCM - 4 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric stre

### Manufacturer Information

GTIN	00662381925022
UPC	662381925022



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1722 Primewest Parkway  
77449-0000, TX Katy  
Phone: 281-828-2012  
Fax: 281-828-2512

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS

Type ..... Double Sided Entry

## Packaging

Carton ..... 3

Weight Per each ..... 1.0499

## Uses, Certifications, and Standards

Application ..... Wire Termination

environmental conditions ..... 90 C

standard ..... UL 486A/B

Temperature Rating ..... 90 C