



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD2600 Type LD BRKR 2P 600A Trip With 2TA603LDK Terms Lin *Eaton Corp*

Catalog Number	LD2600
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, L-Frame, LD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip, Two-Pole, 600A, 600 Vac, 250 VDC, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac, Aluminum, Line and Load, 50/60 HZ
Weight per unit	0.0100 (lbs/each)
Product Category	19980216135504

Features

Current Rating	600 A
dimensions	10.7500 IN X 4.0600 IN X 8.2500 IN
media	Yes
Poles	2
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE LD BRKR 2P 600A TRIP WITH 2TA603LDK TERMS LIN
extra long description	ETN LD2600 LD CB 2P 600A TRIP W/2TA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, L-frame, LD, Complete breaker, Fixed thermal, fixed magnetic trip, Two-pole, 600A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz
Product Type	LD CB 2P 600A Trip W/2TA603LDK Term Line

Manufacturer Information

Brand	Eaton
GTIN	00786679029107
Manufacturers Part Number	LD2600
UPC	786679029107

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	UL 489