



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FD2060L Type FD BRKR 2P 60A/250VDC Max 10K/600VAC Max 18K *Eaton Corp*

Catalog Number	FD2060L
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 60A, 600 Vac, 250 VDC, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac, Line and Load, 50/60 HZ
Weight per unit	3.3 (lbs/each)
Product Category	2 Pole

Features

Current Rating	60 A
dimensions	7.5000 IN X 5.0000 IN X 3.5000 IN
media	Yes
Poles	2
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE FD BRKR 2P 60A/250VDC MAX 10K/600VAC MAX 18K
extra long description	ETN FD2060L FD CB 2P 60A/250VDC MAX
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, fixed magnetic trip type, Two-pole, 60A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, Line and load, 50/60 Hz
Product Type	FD CB 2P 60A/250VDC Max 10K/600VAC Max

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786679850688
Manufacturers Part Number	FD2060L
UPC	786679850688

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.25

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed