



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FP301148CLEAR Thin-Wall Heat Shrink Tubing, 48", Clear

Minnesota Mining (3M)

Catalog Number	FP301148CLEAR
Manufacturer	Minnesota Mining (3M)
Description	Heat Shrink Tube, Clear Insulation Color, -55 °C Operating Temperature, +135 °C Operating Temperature, 48 In Overall Length, 600 V, 0.2 LB
Weight per unit	0.3304 (lbs/each)
Product Category	Splicing & Terminating Kits

Descriptions

Description	THIN-WALL HEAT SHRINK TUBING, 48", CLEAR
extra long description	3M 7000133569 3M™ Heat Shrink Thin-
Features	3M™ Heat Shrink Tubing FP-301 is color coded for quick and easy identification of the wire. This split resistant, flame retardant tubing is used as shrink fit, electrical insulation over cable splices or terminations. The high expansion ratio tubing is mechanically tough, easily markable and resists cold flow. It is ideal for lightweight wire harness covering, fire resistant covering, wire marking, wire bundling and component packaging. It withstands temperatures of 67 to 275 degrees F (55 to 135 degrees

Manufacturer Information

GTIN	00051128596821
Manufacturers Part Number	FP1.000CR48"H
UPC	051128596821

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Thin-Wall Flexible Polyolefin

Packaging

Carton	5
Weight Per each	0.3304

Uses, Certifications, and Standards

standard	UL Recognized, CSA Certified, ABS, and AMS 3636 & 3637
----------	--