Project	Catalog #	Туре	
Prepared by	Notes	Date	



🖌 Interactive Menu

- Order Information page 2
- Product Specifications page 5
- Energy & Performance Data page 7
- Photometric Data page 8
- Product Warranty

HALO

ML56 | 1200 Series

5" and 6" LED Module 1200 lumens

Typical Applications Residential, Light Commercial

Product Certification



Refer to ENERGY STAR[®] Certified Products List. Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Appliance Efficiency Database under JA8.

Product Features


air 🎎


Top Product Features

- For use with 590 series and 690 series trims
- · For use with 5" and 6" Halo new construction and remodel housings
- 120-277V Input
- · Compatible with select phase cut and 0-10V dimmers
- Air-tite per ASTM E283


Dimensional and Mounting Details

120V - phase cut dimming





120-277V - 0-10V dimming





Order Information

SAMPLE ORDER NUMBER: ML5612930 593WB

Order LED Module and trim separately.

A complete system also includes a compatible housing (new construction, remodel, or existing retrofit). Housing aperture size in the ML56 System is determined by the ML56 trim dimensions. ML56 trims are available in 5" and 6" aperture (5" = 59xx series and 6" = 69xx series trims). Refer to Housing Section in this document.

ML56 LED Modules 1200 Series 90 CRI	Driver Option	ML56 LED 5" and 6" Trims	ML56 Beam Forming Optic/Media 1200 Series Accessories	ML56 System Accessories
ML56 LED Modules 1200 Series 90 CRI	Driver Option	ML56 LED 5" and 6" Trims	ML56 Beam Forming Optic / Media 1200 Series Accessories	ML56 System Accessories
ML5612927= 5"/6" LED module, 1200 lumen, 90CRI, 2700K ML5612930= 5"/6" LED module, 1200 lumen, 90CRI, 3000K ML5612935= 5"/6" LED module, 1200 lumen, 90CRI, 3000K ML5612940= 5"/6" LED module, 1200 lumen, 90CRI, 4000K ML5612920720830= 5"/6" dim-to- warm LED module, 1200 lumen, 90CRI, 1850K California non-E26 modules ⁽¹⁾ ML5612927-CA = 5/6" LED module, 1200 lumen, 90CRI, 2700K, California non-E26 ML5612935-CA = 5/6" LED module, 1200 lumen, 90CRI, 3000K, California non-E26 ML5612935-CA = 5/6" LED module, 1200 lumen, 90CRI, 3500K, California non-E26 ML5612940-CA = 5/6" LED module, 1200 lumen, 90CRI, 4000K, California non-E26	[Blank] = 120V 50-60Hz, Leading Edge and Trailing Edge control 5% dimming D010 = UNV 120-277V 50-60Hz, 0-10V analog 5% dimming ⁽²⁾	 590 Series - 5" LED Trims 5922E-5" LED trim, specular reflector & white flange 592H-5" LED trim, haze reflector & the flange 593WB-5" LED trim, white micro-step baffle & flange 593WB-5" LED trim, white micro-step baffle & white flange 594WB-5" LED trim, white micro-step baffle & white flange 594WB-5" LED trim, white micro-step baffle & white flange 594WB-5" LED trim, white micro-step baffle & white flange 594WB-5" LED trim, wall wash - specular reflector, repositionable specular kick reflector, white flange 596WB-5" LED trim, wall wash - specular reflector, repositionable specular kick reflector & white flange – shallow and standard housings 692SC=6" LED trim, haze reflector & white flange 692SC=6" LED trim, haze reflector & white flange 692W-6" LED trim, white micro-step baffle & flange 693BB=6" LED trim, uscan bronze micro-step baffle & flange 693SB=6" LED trim, satin nickel micro-step baffle & flange 693SB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED trim, satin nickel micro-step baffle & flange 694WB=6" LED directional trim, satin nickel eyeball, baffle & flange – shallow and standard housings 694SNB=6" LED trim, white shallow and standard housings 694SNB=6" LED trim, white wash specular reflector, repositionable specular kick reflector, white flange 696WB=6" LED trim, white wash wash spec	BFR56NFL=Beam forming reflector kit, narrow flood, 25° nominal BFR56MH=Media holder, accepts one 3.45° lens. (Requires BFR56NFL & L345SF, order separately.) L345SF=3.45″ diameter soft focus lens. Requires (BFR56NFL and BFR56MH, order separately.)	ML7RAB=Retrofit adapter band for housings without torsion spring receivers. The ML7RAB kit supplies parts to retrofit four housings; the kit includes: 4 - Retrofit adapter bands with screws and locking wire nuts WWS95SC-5 ⁻⁵ Wall wash insert - kick reflector for 595WW (1-included with trim) double or corner wall wash** TRMS90WH-5 ⁻⁵ LED oversize trim ring for use with 59 ⁻ series trims, white 6.3 ⁻¹ LD, 7.5 ⁻⁰ LD. Ring slips over LED trim. Inset design allows 5 ⁻⁵ trim to fit into oversize trim ring for use with 69 ^a series trims, white 6.3 ⁻¹ LD, 7.5 ⁻⁰ LD. Ring slips over LED trim. Inset design allows 5 ⁻⁵ trim to fit into oversize trim ring for use with 69 ^a series trims, white 6.9 ⁻¹ LD, 9.5 ⁻⁰ LD. Ring slips over LED trim. Inset design allows 5 ⁻⁶ trim to fit into oversize ring for an even trim surface **Wall Wash Trims 595WW and 695WW Feature an exclusive Repositionable Kick Reflector for fine-tuning adjustment of the wall wash effect. The WW595SC and WW695SC are Repositionable Kick Reflectors sold separately for addition to the Wall Wash Trim when a double or corner wall wash is needed, or for replacement of original kick reflector included with the trim.
Notes (1) California product only.	(2) Not compatible with ML5612D2W930 dim-to-warm or -CA California LED modules	Notes		Notes

Housing - Compatibility

The ML56 LED module - trim combination is cULus Listed or UL Classified for use with any 5" or 6" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 115 in³ in addition to those noted below.

Halo UL Listed Compatibility

D010 Housings							
D010 H	lousings						
5" Trims: 591X, 592X, 593X, 594X, 595X, 596X	6" Trims: 691X, 692X, 693X, 694X, 695X, 696X						
Halo LED.5-inch H550ICATD010 = 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing, 120-277V, 0-10V dimming H550RICATD010 = 5" LED, Insulated Ceiling, Air-Tite, Remodel Housing, 120-277V, 0-10V dimming	Halo LED 6-inch H750ICATD010 = 6" LED, Insulated Ceiling, Air-Tite, New Construction Housing, 120-277V, 0-10V dimming H750RICATD010 = 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing, 120-277V, 0-10V dimming						
Halo LED Fire Rated 6-inch H550FR2ICATD010 = 6° fire safe new construction housing for LED integrated trims or modules, 120-277V, 0-10V dimming	Halo LED Fire Rated 6-inch H750FR2ICATD010 = 6" fire safe new construction housing for LED integrated trims or modules, 120-277V, 0-10V dimming						
Notes							



HALO

ML56 1200 Series | 90 CRI

Housing - Compatibility (continued)

The ML56 LED module - trim combination is cULus Listed or UL Classified for use with any 5" or 6" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 115 in³ in addition to those noted below.

Halo UL Listed Compatibility

E26 Housings				
-inch Trims: 591X, 592X, 593X, 594X, 595X, 596X Note 5-inch shallow housings for use with 591X, 594X, 596X trims only)	6-inch Trims: 691X, 692X, 693X, 694X, 695X, 696X (Note 6-inch shallow housings for use with 691X, 694X, 696X trims only)			
a lo LED 5-inch 550ICAT = 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing	Halo LED 6-inch H750ICAT = 6" LED, Insulated Ceiling, Air-Tite, New Construction Housing			
50RICAT = 5" LED, Insulated Ceiling, Air-Tite, Remodel Housing	H750RICAT = 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing			
50ICAT = 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing	H750T = 6" LED, Non-IC, Air-Tite, New Construction Housing			
50RICAT = 5" LED, Insulated Ceiling, Air-Tite, Remodel Housing	H750TCP = 6" LED, Non-IC, New Construction/Remodel Chicago Plenum Housing H2750ICAT = 6" LED, Shallow, Insulated Ceiling, Air-Tite, New Construction (use with 691X, 694X, 696X trims or			
lo Shallow Housings 5-inch	H2750RICAT = 6" LED, Shallow, Insulated Ceiling, Air-Tite, Remodel (use with 691X, 694X, 696X trims only)			
5ICAT = 5" Shallow, Insulated Ceiling, Air-Tite New Construction	E750ICAT = 6" LED, Insulated Ceiling, Air-Tite, New Construction Housing			
SRICAT = 5" Shallow, Insulated Ceiling, Air-Tite Remodel SICATNB = 5" Shallow, Insulated Ceiling, Air-Tite New Construction, No Socket Bracket	E750RICAT = 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing			
	Halo LED Fire Rated 6-inch			
alo Standard Housings 5-inch 5ICAT = 5" Insulated Ceiling, Air-Tite New Construction Housing	H750FR2ICAT = 6" fire safe new construction housing for LED integrated trims or modules			
SCAT = 5" Insulated Ceiling, Air-Tite Remodel Housing	Halo LED retrofit			
5ICATNB = 5" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket	ML7E26RFK = 6" Retrofit Enclosure, Non-IC, E26 Screw base Interface			
5T = 5" Non-IC, New Construction Housing	ML7BXFK = 6" Retrofit Enclosure, Non-IC, BX Whip			
SRT = 5" Non-IC, Remodel Housing STNB = 5" Non-IC, New Construction Housing, No Socket Bracket	Hole Shellow Heusings 6 inch			
ICAT = 5" Insulated Ceiling, Air-Tite New Construction Housing	Halo Shallow Housings 6-inch H27ICAT = 6" Shallow, Insulated Ceiling, Air-Tite New Construction			
RICAT = 5" Insulated Ceiling, Air-Tite Remodel Housing	H27RICAT = 6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing			
ICATNB = 5" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket TAT = 5" Non-IC, New Construction Housing	H27T = 6" Shallow, Non-IC, New Construction Housing			
RTAT = 5" Non-IC, Remodel Housing	H27RT = 6" Shallow, Non-IC, Remodel Housing E27ICAT = 6" Shallow, Insulated Ceiling, Air-Tite New Construction			
TATNB = 5" Non-IC, New Construction Housing, No Socket Bracket	E27RICAT = 6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing			
	E27TAT = 6" Shallow, Non-IC, New Construction Housing			
	E27RTAT = 6" Shallow, Non-IC, Remodel Housing			
	Halo Standard Housings 6-inch			
	H7ICAT = 6" Insulated Ceiling, Air-Tite New Construction Housing			
	H7RICAT = 6" Insulated Ceiling, Air-Tite Remodel Housing H7ICT = 6" Insulated Ceiling, New Construction Housing			
	H7RICT = 6" Insulated Ceiling, Remodel Housing			
	H7ICATNB = 6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket			
	H7ICTNB = 6" Insulated Ceiling, New Construction Housing, No Socket Bracket H7T = 6" Non-IC, New Construction Housing			
	H7RT = 6" Non-IC, Remodel Housing			
	H7TNB = 6" Non-IC, New Construction Housing, No Socket Bracket			
	H7TCP = 6" Non-IC, Chicago Plenum, New Construction/Remodel Housing			
	H7UICAT = 6" Insulated Ceiling, Universal, Air-Tite, New Construction Housing E7ICAT = 6" Insulated Ceiling, Air-Tite New Construction Housing			
	E7RICAT = 6" Insulated Ceiling, Air-Tite Remodel Housing			
	E7ICATNB = 6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket			
	E7TAT = 6" Non-IC, New Construction Housing E7RTAT = 6" Non-IC, Remodel Housing			
	E7TATNB = 6" Non-IC, New Construction Housing, No Socket Bracket			
	Notes			

Housings - UL Classified for Retrofit Compatibility

6" Trims: 692X, 693X, 694X, 695X, 696X IC22, IC22R, IC22W, IC22S, IC23, IC23W, TC2, TC2R, IC2 PS1 Juno Thomas CR1, PR1, QL1 **Commercial Electric** C7ICA, H3 Capri HL7ICA (EL7ICA) P87-AT † Elco Progress Lightolier 1104ICx +, 1104IC + Lithonia LC6, L7X

+ Requires ML7RAB retrofit adapter band (ordered separately); for use in housings without torsion springs.

Juno®, Capri, Lightolier®, Lithonia Lighting®, Thomas® Lighting, Elco Lighting®, Progress® Lighting and Commercial Electric[™] and their product brand names, where identified above, are tradenames or trademarks of each respective company and Cooper makes no representations on these trademarks.




HALO

Housing - Trim Compatibility

Housing compatibility in the ML56 System is determined by the ML56 trim dimensions. ML56 trims are available in 5-inch and 6-inch aperture (5-inch = 59xx series and 6-inch = 69xx series trims).

(Note: "xx" in the trim model number denotes finish code.)



6" baffle

694

694WB

white

6" eyeball

(



693BB

694SN

satin nickel



black baffle, white trim



694TBZ

tuscan bronze



tuscan bronze baffle and trim

695 6" wall wash



695WW specular reflector

696 6" shallow baffle



white shallow baffle and trim



HALO

ML56 1200 Series | 90 CRI

Product Specifications

Mechanical

Light Module

- Module includes LED package, LED driver, heat sink, and lens
- Durable die-cast aluminum construction.
- Heat sink designed to conduct heat away from the LED keeping the junction temperatures below specified maximums, including insulated ceiling environments

Optics

- Diffuse lens is standard on all 1200 Series LED light modules
- Impact-resistant polycarbonate
- · Convex form for lamp-like appearance
- High lumen transmission
- Optional beam forming optic replaces diffuse lens and provide narrow flood (NFL) 25° nominal distribution. Beam forming optic is field installed. Order separately (accessories).

Mounting

- Modules attach to reflector and baffle trims via locking tabs, and attach to eyeballs via keyed twist-to-lock mating bosses
- The complete light module and trim assembly installs into housings with precision formed torsion springs located on the trim
- Use the retrofit adapter band (ML7RAB) accessory when housing does not have receivers for torsion springs.

Housing Compatibility

- A complete ML56 system includes a LED Module, LED trim, and a compatible housing (new construction, remodel, or existing retrofit).
- Housing compatibility in the ML56 System is determined by the ML56 trim dimensions.
- ML56 trims are available in 5" and 6" aperture (5" = 59xx series and 6" = 69xx series trims). Refer to Housing – Trim Section in this document.

LED

- 1200 Series = 1200 design lumens typical. Delivered lumens vary upon 5" or 6" trim, color temperature, and trim finish.
- Color Temperature options: 2700K, 3000K, 3500K, 4000K
- CRI: 90, R9750
- L70 at 50,000 hours, projected in accordance with IES TM-21
- LED is a chip on board design consisting of a multiple LED package with proximity phosphor coating to create one virtual white light source for a productive "cone of light"

Color Specification & Quality Standards

- A tight chromaticity specification ensures LED color uniformity, sustainable Color Rendering Index (CRI) and Correlated Color Temperature (CCT) over the useful life of the LED
- LED color uniformity of 3 SDCM, exceeds ENERGY STAR® color standards per ANSI C78.377-2008.
- High color performance with 90CRI minimum, and R9 greater than 50.
- Every Halo LED Module is quality tested and performance measured, and then serialized in a permanent record to register lumens, wattage, CRI and CCT.
- Halo LED serialized testing and measurement process ensures color and lumen consistency on a per-unit basis, and validates long-term product consistency over time
- Halo ML56 LED Modules include lumen, CRI, and CCT designations in the model number Example: ML5612930
 - 56 = 5" / 6" aperture series
 - 12 = 1200 lumen series
 - 9 = >90 CRI
 - 30 = 3000K nominal CCT

Electrical Power Connections

- LED connector is a non-screw base luminaire disconnect offering easy installation in Halo 5" H550 series and 6" H750 and 2750 series housings (per LED trim 5" or 6").
- LED Connector meets high-efficacy luminaire requirements for a non-screw base, and where required.
- The included E26 medium screw-base Edison adapter* provides easy retrofit of incandescent housings (non-California product only) (see Housing Section).

Ground Connection

• Separate grounding cable included on the module for attachment to the housing during installation.

LED Driver

- Driver is universal voltage 120V-277V, and may be controlled from a switch in Halo LED housings at 120V, 220V, 230V, 240V, and 277V.
- Two driver options:
- (1) Dimmable at 120V operation when connected to a compatible phase cut dimmer.
- (2) Dimmable at 120-277V operation when connected to a compatible 0-10V dimmer.
- Driver is a high efficiency, electronic power supply providing DC power to the LED.
- Driver meets FCC EMI/RFI Consumer Level limits on 120-277V main inputs, and is compliant for use in residential and commercial installations.
- Driver features high power factor, low THD, and has integral thermal protection in the event of over temperature or internal failure.
- Driver is replaceable, if replacement should be required.

Dimming

 Designed for dimming capability to nominal 5% in normal operation with standard 120V Leading Edge (LE) and Trailing Edge (TE) phase control dimmers or 120-277V 0-10V dimmers (Consult dimmer manufacturer for dimmer compatibility and details. Note, some dimmers require a neutral in the wall box).

Compliance

- cULus listed 1598 Luminaire (Halo housings)
- UL Classified when used in retrofit (refer to housing section)
- cULus listed for damp locations
- cULus Wet location listed with baffle and reflector trims only
- Airtight certified per ASTM E283 (not exceeding 2.0 CFM under 57 Pascals pressure difference)
- IP56 ingress protection rated with baffle and reflector trims only
- RoHS compliant
- May be used in IC (insulated ceiling) housings in direct contact with insulation* and combustible material
- Can be used for California Title 24 compliance
- Can be used for International Energy Conservation Code (IECC) high efficiency luminaire compliance.
- Can be used for Washington State Energy Code compliance
- ENERGY STAR® certified luminaire consult ENERGY STAR® certified product list
- EMI/RFI per FCC 47CFR Part 15 Class B Consumer limits (commercial and residential compliant)
- Photometric testing in accordance with IES LM-79
 Lumen maintenance projections in accordance with IES LM-80 and TM-21
- CE Mark "Conformité Européene" conformity with the Council of European Communities Directives, meeting internationally recognized compliance when used with Halo H550, H750, and H2750 Series LED housings only

Warranty

 Five year limited warranty, consult website for details. www.cooperlighting.com/legal

LED Module in New or Retrofit Existing Construction – Housings other than Halo

- If used in recessed housings other than Halo, the Cooper Lighting Solutions 5-year limited warranty applies to the LED Module and Trim only.
- As with any electrical installation, a qualified electrician must ensure compatibility of use with a particular housing; this includes all applicable national and local electrical and building codes. Installer is responsible to properly and securely retain the LED Module and LED Trim in the housing at time of installation.

ML56 1200 Series Compliance Table

90 CRI LED Modules with ML56 Trims

	ML5612927	ML5612930	ML5612935	ML5612940
593BB	WSEC, IECC	WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC
693BB	ES, T24, WSEC, IECC			
593TBZB	ES, T24, WSEC, IECC			
693TBZB	ES, T24, WSEC, IECC			
593SNB	ES, T24, WSEC, IECC			
693SNB	ES, T24, WSEC, IECC			
592H	ES, T24, WSEC, IECC			
593WB	ES, T24, WSEC, IECC			
592SC	ES, T24, WSEC, IECC			
592W	ES, T24, WSEC, IECC			
595WW	ES, T24, WSEC, IECC			
695WW	ES, T24, WSEC, IECC			
692H	ES, T24, WSEC, IECC			
692W	ES, T24, WSEC, IECC			
692SC	ES, T24, WSEC, IECC			
693WB	ES, T24, WSEC, IECC			
596WB	ES, T24, WSEC, IECC			
694TBZB	ES, T24, WSEC, IECC			
696WB	ES, T24, WSEC, IECC			
594TBZB	ES, T24, WSEC, IECC			
694SNB	ES, T24, WSEC, IECC			
594SNB	ES, T24, WSEC, IECC			
694WB	ES, T24, WSEC, IECC			
594WB	ES, T24, WSEC, IECC			
594WB-30	ES, T24, WSEC, IECC			
694WB-30	ES, T24, WSEC, IECC			
	·			

Code Descriptions:

ES = ENERGY STAR[®] Certified Luminaire

IECC = International Energy Conservation Code "High Efficacy"

WSEC = Washington State Energy Code - "High Efficacy" Luminaire



ML56 1200 Series Lumen Table

90 CRI LED Modules with ML56 trims

		ML561	2927	ML561	2930	ML56	12935	ML56	2940
	Trim Catalog #	Lumens	LPW	Lumens	LPW	Lumens	LPW	Lumens	LPW
0° Tilt Angle	593BB	727.0	42.0	777.4	62.4	848.4	71.3	875.8	67.4
	693BB	813.6	47.0	870.0	69.9	949.5	79.8	980.1	75.4
	593TBZB	821.3	47.5	878.3	70.5	958.5	80.5	989.5	76.1
	693TBZB	845.7	48.9	904.4	72.6	987.0	82.9	1018.9	78.4
	593SNB	900.1	52.0	962.6	77.3	1050.5	88.3	1084.4	83.4
	693SNB	937.9	54.2	1002.9	80.6	1094.5	92.0	1129.8	86.9
	592H	1036.6	59.9	1108.6	89.0	1209.8	101.7	1248.9	96.1
	593WB	1057.7	61.1	1131.1	90.9	1234.4	103.7	1274.3	98.0
	592SC	1071.1	61.9	1145.4	92.0	1250.0	105.0	1290.3	99.3
	592W	1074.4	62.1	1148.9	92.3	1253.9	105.4	1294.3	99.6
	595WW	1077.7	62.3	1152.5	92.6	1257.7	105.7	1298.3	99.9
	695WW	1078.8	62.4	1153.7	92.7	1259.0	105.8	1299.7	100.0
	692H	1082.2	62.6	1157.2	93.0	1262.9	106.1	1303.7	100.3
	692W	1099.9	63.6	1176.2	94.5	1283.6	107.9	1325.1	101.9
	692SC	1104.4	63.8	1181.0	94.9	1288.8	108.3	1330.4	102.3
	693WB	1109.9	64.2	1186.9	95.3	1295.3	108.8	1337.1	102.9
	596WB	1113.8	64.4	1191.1	95.7	1299.8	109.2	1341.8	103.2
	694TBZB	1117.7	64.6	1195.2	96.0	1304.4	109.6	1346.5	103.6
	696WB	1137.6	65.8	1216.6	97.7	1327.7	111.6	1370.5	105.4
	594TBZB	1138.8	65.8	1217.8	97.8	1329.0	111.7	1371.9	105.5
	694SNB	1149.9	66.5	1229.6	98.8	1341.9	112.8	1385.2	106.6
	594SNB	1167.6	67.5	1248.6	100.3	1362.7	114.5	1406.6	108.2
	694WB	1184.8	68.5	1267.0	101.8	1382.7	116.2	1427.4	109.8
	594WB	1192.0	68.9	1274.7	102.4	1391.2	116.9	1436.0	110.5
30° Tilt Angle	594WB-30	1126.5	65.1	1204.7	96.8	1314.7	110.5	1357.2	104.4
	694WB-30	1108.8	64.1	1185.7	95.2	1294.0	108.7	1335.8	102.8

Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary.

Energy and Performance Data

ML56 1200/90 Series
(Values at non-dimming line voltage)
Minimum Starting Temp: -30°C (-22°F)
EMI/RFI: FCC Title 47 CFR, Part 15, (Consumer)
Sound Rating: Class A
Input Voltage: UNV 120V-277V
Power Factor: >0.95 @ 120V and >0.9 @277V
Input Frequency: 50/60Hz
THD: <20%
Input Power: 12.3W
Input Current at 120V: 0.14A
Input Current at 277V: 0.07A
Driver Compliance: UL8750, Class II rated
Maximum IC (Insulated Ceiling) Ambient Continuous Operating Temperature: 25°C (77°F)
Maximum Non-IC Ambient Continuous Operating Temperature: 40°C (104°F)

ML5612927

ML5612935

Lumens Watts

PRODUCT SPECIFICATIO	NS
Lumens	1212
Watts	12.3
Lumens Per Watt (Efficacy)	98.6
Color Accuracy (CRI)	94
Light Color (CCT) Correlated Color Temperature (CCT)	2700 K
↓ I	
warm white soft white bright 2700K 3000K 4500K	t white 65001

PRODUCT SPECIFICATIONS

Lumens Per Watt (Efficacy)

warm white soft white bright white

4500K

Color Accuracy (CRI)

Light Color (CCT)

2700K 3000K

1320

11.7


113

94

6500K

3500K

ML5612930



ML5612940


PRODUCT Specificatio	NS			
Lumens	1395			
Watts	12			
Lumens Per Watt (Efficacy)	116			
Color Accuracy (CRI) 94				
Light Color (CCT) Correlated Color Temperature (CCT)	4000K			
↓ I				
warm white soft white bri 700K 3000K 4500K	ght white 6500			



P View IES files

Photometry 5" Trims • 1200 Series • 90 CRI

N



IL5612930-595W	w

Test Number	P129848	
Light Module	1200 Series, 90CRI	
Trim	5" Aperture, Wall Wash with Specular Clear Trim and Specular Clear Kick Reflector	
Lumens	1198	
Efficacy	69.6 Lm/W	
SC	0.83	

Single Unit Footcandles 2.5' From Wall (Distance From Fixture Along Wall)

DD		1'					
			2'	3'	4'	5'	6'
1'	3.9	2.6	1	0.3	0.1	0	0
2'	14.9	10.6	4.5	1.4	0.4	0.1	0
3'	18.2	14.6	7.8	3.1	1.2	0.4	0.1
4'	13.6	11.9	8.2	4.3	1.9	0.8	0.3
5'	9.3	8.4	6.6	4.3	2.4	1.2	0.5
6'	6.3	5.9	4.9	3.6	2.4	1.4	0.7
7'	4.4	4.2	3.6	2.9	2.1	1.4	0.9
8'	3.2	3	2.7	2.3	1.8	1.3	0.9
9'	2.4	2.3	2.1	1.8	1.5	1.2	0.8
10'	1.8	1.7	1.6	1.4	1.2	1	0.8

Zonai Lume	en Summary	
Zone	Lumens	%Fixture
0-30	590	51.5
0-40	868	75.7
0-60	1119	97.7
0-90	1146	100
90-180	0	0
0-180	1146	100

Zanal Luman Summary

Multiple Unit Footcandles

2.5' From Wall (Distance From Fixture Along Wall)

DD		3'			4'			
1'	4.2	3.4	4.2	4	2.1	4		
2'	16.3	14.4	16.3	15.3	9	15.3		
3'	21.4	22.4	21.4	19.4	15.6	19.4		
4'	17.9	20.1	17.9	15.5	16.4	15.5		
5'	13.5	15.1	13.5	11.7	13.1	11.7		
6'	9.9	10.8	9.9	8.7	9.9	8.7		
7'	7.3	7.8	7.3	6.5	7.3	6.5		
8'	5.4	5.7	5.4	5	5.5	5		
9'	4.1	4.3	4.1	3.8	4.2	3.8		
10'	3.2	3.3	3.2	3	3.2	3		

Photometry 5" Trims • 1200 Series • 90 CRI • NFL Lens

Multiplier Table						
CCT Option	2700 K	3000 K	3500 K	4000 K		
CCT Multiplier	0.967	1.000	1.052	1.164		

Table based upon testing with 3000°K color temperature, 90CRI.

Multipliers may be used to determine relative lumen values with other color temperatures.

Test Number	P130382					⊼	-т
Light Module	1200 Series, 90CRI, NFL o	optic			,	4\	
Trim	5" Aperture, Haze Trim				o°/	$\left \right\rangle$	þ
Lumens	1126				1	$\perp $	
Efficacy	65.1 Lm/W				\leq	$\overline{}$	\perp
SC	0.41			D	FC	L	w
			-	5.5'	147.1	2.2	2.2
Candlanav	or Distribution			7'	90.8	2.8	2.8
Candlepov	ver Distribution	1		7' 8'	90.8 69.5	2.8 3.2	2.8 3.2
Candlepov				•			
Candlepov	ver Distribution Downlight			8'	69.5	3.2	3.2
Candlepov		90°		8' 9'	69.5 54.9	3.2 3.6	3.2 3.6

60°


45°

30

	Zone	Lumens	%Fixture
ľ	0-30	982	87.2
	0-40	1088	96.6
	0-60	1124	99.8
	0-90	1126	100
	90-180	0	0
	0-180	1126	100

ML5612930-BFR56NFL-594WB

Test Number	P130446	
Light Module	1200 Series, 90CRI, NFL optic	
Trim	5" Aperture, Directional Eyeball	
Lumens	1294	
Efficacy	74.8 Lm/W	
SC	0.4	



Lumens

984

1088

1248

1294

0

1294

%Fixture

76.1

84.1

96.5

100

0

100

Zonal Lumen Summary

Zone

0-30

0-40


0-60

0-90

90-180

0-180

-СВ-30° Horizontal 30 Plane w D FC CB 5.5' 103.5 2.8 3.2 2.4 7' 63.9 3.6 3 4 8' 48.9 4.1 36 46 9' 38.6 4.6 4 5.2 10' 31.3 5.1 4.4 5.8 12' 21.7 6.1 5.4 6.9



Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary.



15

3000

4500

n

ML56 1200 Series | 90 CRI

30°

Horizontal

Plane

9.3 7'

D FC

5.5' 15.1 6.3 6.4 3.2

8' 7.1 9.2 9.4 4.6

9' 5.6 10.5 10.6 5.2

10' 4.6 11.6 11.8 5.8

12' 3.2 13.9 142 69

30°

Vertical

Plane

D FC

1' 279.6

2' 69.9 2.2 2.6 3.5

3' 31.1

4' 17.5 4.7 5.2 6.9

5' 11.2 5.7 6.4 8.7

6' 7.8 6.9 7.8 10.4

%Fixture

54.5

76.2

97.9

100

0

100

View IES files

-св-

w CB

- D —

1.2 11

30°

L w

3.5 3.8 5.2

св

CB

17

30


L

8.1 8.2 4

Photometry 6" Trims • 1200 Series • 90 CRI

CCT Option	2700 K	3000 K	3500 K	4000 K
CCT Multiplier	0.9669	1.0000	1.0517	1.1644


Multipliers may be used to determine relative lumen values with other color temperatures.




Zon

2

Candlepower Distribution



Candlepower Distribution



Room

180-deg:

FC w L 5.5' 41.5 4 4 7' 25.6 5 5 8' 19.6 5.8 5.8 9' 15.5 6.6 6.6 10' 12.6 7.2 7.2 12' 8.7 8.8 8.8

nal Lumen Summary						
Zone	Lumens	%Fixture				
0-30	655	55.8				
0-40	910	77.5				
0-60	1159	98.7				
0-90	1174	100				
90-180	0	0				
0-180	1174	100				

ML5612930-695WW					
Test Number	P129944				
Light Module	1200 Series, 90CRI				
Trim	6" Aperture, Wall Wash with Specular Clear Trim and Specular Clear Kick Reflector				
Lumens	1147				
Efficacy	66.3 Lm/W				
SC	0.76				

Single Unit Footcandles

DD		1'	2'	3'	4'	5'	6'
1'	3.2	1.9	0.7	0.2	0.1	0	0
2'	14	9.9	4.3	1.3	0.3	0.1	0
3'	16.5	13	7.2	3.1	1.2	0.4	0.1
4'	12.6	10.8	7.3	4	1.9	0.8	0.4
5'	9	8	5.9	3.9	2.3	1.2	0.6
6'	6.5	5.9	4.6	3.3	2.2	1.3	0.8
7'	4.9	4.4	3.6	2.7	1.9	1.3	0.8
8'	3.7	3.4	2.8	2.2	1.6	1.2	0.8
9'	2.8	2.6	2.2	1.8	1.4	1	0.8
10'	2.2	2.1	1.8	1.5	1.2	0.9	0.7

Multiple Unit Footcandles

ML5612930-694WB Test Number P129920

Light Module Trim

Lumens

Efficacy

SC

180

360

540

0

Zone

0-30

0-40

0-60

0-90

90-180

0-180

1200 Series, 90CRI

1260

1.17 **Candlepower Distribution**

72.8 Lm/W

Eyeball at 0-degrees

15

Lumer

397

631

1041

1260

0

1260

Zonal Lumen Summary

6" Aperture, Directional Eyeball

90°

75°

60°

45°

30°

%Fixture

31.5

50.1

82.6

100

0

100

Zone

0-30

0-40

0-60

0-90

90-180

0-180

Zonal Lumen Summary

Lumens

625

873

1122

1147

0

1147

2.5' From Wall (Distance From Fixture Along Wall)							
DD	3'				4'		
1'	3.4	2.4	3.4	3.3	1.4	3.3	
2'	15.3	13.5	15.3	14.3	8.5	14.3	
3'	19.6	20	19.6	17.6	14.5	17.6	
4'	16.7	18.1	16.7	14.6	14.5	14.6	
5'	12.9	13.9	12.9	11.3	11.8	11.3	
6'	9.8	10.5	9.8	8.7	9.2	8.7	
7'	7.5	8	7.5	6.8	7.1	6.8	
8'	5.8	6.2	5.8	5.3	5.6	5.3	
9'	4.6	4.9	4.6	4.2	4.5	4.2	
10'	3.7	3.9	3.7	3.3	3.6	3.3	

Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary




ML56 1200 Series | 90 CRI

Photometry 6" Trims • 1200 Series • 90 CRI • NFL Lens


Multiplier Table						
CCT Option	2700 K	3000 K	3500 K	4000 K		
CCT Multiplier	0.967	1.000	1.052	1.164		


Table based upon testing with 3000°K color temperature, 90CRI. Multipliers may be used to determine relative lumen values with other color temperatures.

ML5612930-BFR56NFL-692H



Candlepower Distribution





Zonal Lumen Summary

Zone	Lumens	%Fixture
0-30	1005	85.5
0-40	1110	94.4
0-60	1174	99.9
0-90	1175	100
90-180	0	0
0-180	1175	100

ML5612930-BFR56NFL-694WB

Test Number	P130542	
Light Module	1200 Series, 90CRI, NFL optic	
Trim	6" Aperture, Directional Eyeball	
Lumens	1286	
Efficacy	74.3 Lm/W	
SC	0.41	

%Fixture

77 9

86.2


98.4

100

0

100

Candlepower Distribution



Lumens

1002

1109

1265

1286

0

1286

Zonal Lumen Summary

Zone

0-30


0-40

0-60


0-90

90-180

0-180



P View IES files



Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary.



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2020 Cooper Lighting Solutions All Rights Reserved. Specifications and dimensions subject to change without notice.