La legrand[®]

WIREMOLD[°] Plugmold[°] Multioutlet Systems



Plugmold systems are available in a variety of colors and configurations.

Plugmold[®] Raceway & Multioutlet Assemblies

Plugmold[®] Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil[®] harnesses of prewired receptacles, and cord-ended units.

Plugmold^{*} Multioutlet Systems are available in black or ivory ScuffCoat^{**} finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosionresistant, making them ideal for labs.

PRODUCTS: PLUGMOLD 2000 SERIES, 2400 SERIES, AL2000 SE-RIES, NM2000 SERIES, NM2400 SERIES

Features & Benefits

- Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.
- Multiple finishes. Choose from black or ivory ScuffCoat, white or gray painted enamel or durable stainless steel finishes.
- **USB Charging.** Available with dual-port USB-A modules, sharing 2.4 amps of charging capacity and single-port USB-C module with 30W Power Delivery.
- **Tamper-resistance protection.** Prevents the accidental insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.
- Single, alternating circuit, and isolated ground wiring options available. Wiring options to meet virtually any job or environment requirement.
- Variety of lengths. Installed power and USB charging in multiple lengths to meet space and location requirements.

Vertical Markets

- Commercial
- Retail
- Education
- Hospitality
- Entertainment
- Healthcare

Compliance

cULus Listed Base & Blank Cover: File E4376 Guide RJBT Multioutlet Assemblies: File E15191 Guide PVGT Fittings: File E41751 Guide RJPR

- **Full range of fittings.** Provide flexibility for multiple installation options or integrations with 2000 or 2400 Series Raceway systems.
- Snapicoil harnesses with different lengths and receptacle spacing. Custom solution available for large or specific use electrical installations.
- **Customization available.** Plugmold products can be modified to accommodate virtually any application or aesthetic need.
- **Receptacle spacing options.** Select the right configuration for your application.
- **cULus Listed.** Safety and reliability in the applications.



Download this product's PEP ecopasport, environmental product declaration at www.legrand.us/resources-and-downloads. This declaration conforms with ISO 14025 and 14040 and is in alignment with EN 15804.

Base & Blank Cover: Meets Article 386 of NEC Plugmold Strips: Meets Article 380 of NEC



Plugmold Multioutlet Systems Quick Selection Guide

FABRICATION	PROFILE	FINISH OPTIONS	LENGTHS	WIRING CONFIGS.	OUTLET O.C. SPACING	OPTIONS QUANTITY	OPTIONS
Steel	2000 Series	Black Scuffcoat Ivory Scuffcoat Gray Enamel White Enamel Stainless Steel	2' (610mm) * 3' (910mm) 5' (1.5m) 6' (1.8m) * Stainless steel only	GB, GB/USB, GBA	6" (152mm) 9" (229mm) 12" (305mm) 18" (457mm) 24" (608mm)	 4 Single 5 Single 6 Single 8 Single 10 Single 12 Single 3 Duplex 4 Duplex 5 Duplex 6 Duplex 	 Hard-Wired models Cord-Ended models USB Charging models Plug-In model GFCI Protection Tamper-Resistant
Steel	2400 Series	Ivory Scuffcoat	3' (910mm) 5' (1.5m) 6' (1.8m)	GB, GBA, IG	6" (152mm) 12" (305mm) 18" (457mm) 24" (608mm)	 4 Single 5 Single 6 Single 10 Single 12 Single 3 Duplex 4 Duplex 5 Duplex 6 Duplex 	 Hard-Wired models Cord-Ended models
Aluminum	AL2000 Series	Anodized	4' (1.2m) 5' (1.5m) 6' (1.8m)	GB, GBA, GB/USB	6" (152mm) 12" (305mm) 18" (457mm)	4 Single 5 Single 6 Single 10 Single 12 Single	 Hard-Wired models Cord-Ended models USB Charging models GFCI Protection Tamper-Resistant
Nonmetallic	NM2000 Series	Ivory PVC	4' (1.2m) 5' (1.5m) 6' (1.8m)	GB, GBA, IG	9" (229mm) 12" (305mm) 15" (381mm) 18" (457mm) 30" (760mm)	 2 Duplex 4 Duplex 5 Duplex 6 Duplex 8 Duplex 	 Hard-Wired models Cord-Ended models
Nonmetallic	NM2400 Series	Ivory PVC	3' (910mm) 4' (1.2m) 5' (1.5m) 6' (1.8m)	GB, GBA	12" (305mm) 18" (457mm) 30" (760mm)	2 Duplex 3 Duplex 4 Duplex 5 Duplex 6 Duplex	 Hard-Wired models Cord-Ended models

Plugmold 2000 Series Steel Multioutlet Systems Ordering Information



NOTE: Color codes: "V" for lvory ScuffCoat[¬] finish, "BK" for Black ScuffCoat[¬] finish, "G" for Gray enamel finish, "WH" for white enamel finish, and "S" for stainless steel. Receptacle colors match extrusion colors except for stainless steel which has black receptacles.

* All 2000 Series Plugmold products include two (2) 2010B Blank End Fittings and one (1) 2001 Base Coupling unless otherwise indicated in the product desciption.

Steel Plugmold[®] Multioutlet Systems

Steel Plugmold Multioutlet Systems are available in a wide range of lengths and finishes to provide a versatile solution for many applications. Options include versions with single or alternating circuits, standard receptacles, Snapicoil harnesses of prewired receptacles, USB charging options, GFCI protection, tamper-resistance, plug-in and cord-ended units.

Steel Plugmold^{*} Multioutlet Systems are available in black or ivory ScuffCoat^{**} finish, painted white or gray enamel finish, or stylish stainless steel. The enamel finishes work with many types of decor or can be painted to blend with most color schemes. Stainless steel Plugmold raceway is both durable and aesthetically pleasing.



Steel Plugmold systems are available in a variety of colors and configurations.

Plugmold 2000 Series Steel Multioutlet Systems

Plugmold 2000 Series Wire Fill Capacities for Power									
CABLE TYPE	WIRE SIZE THHN/THWN	O. Inches	D. (mm)	NO. OF CONDUCTORS (40% FILL) 2000					
POWER WIRING WITHOUT DEVICES	12 AWG 14 AWG	0.130 0.111	(3.3) (2.8)	7* 7*					
POWER WIRING WITH DEVICES (Plugmold Series)	12 AWG 14 AWG	0.122 0.105	(3.1) (2.7)	5** 5**					



*Wire capacity limited to maximum of seven conductors due to .025" (.6mm) material thickness of cover. **Including one hot, neutral, and ground wire from the receptacle.





Steel Plugmold Multioutlet Systems are ideal for use in homes, dormitories and office applications, anywhere convenient access to power or USB charging is needed.



Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

Plugmold 2000 Series Wiring Configurations								
		With Snapicoil						
GB Series: 3-wire, #12 THHN (1 hot,1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.	GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.					

NOTE: SNAPICOIL REELS on custom order. Snapicoil harness is available on reels if lengths greater than 50' are needed, or if multiple lengths are required for production-type jobs. The maximum length per reel is 240' for Snapicoil with outlets 12" and 18" on centers; 500' with outlets 30" on center. Packaging includes the necessary number of lengths of base, holecut cover, wire clips, and couplings for complete installation. Price and delivery information should be obtained prior to specifying or ordering. To specify or order, add "R" to the Snapicoil number. Ex: V20GB12R. Other outlet spacings available on custom order.

Receptacles are made from high impact thermoplastic. Snapicoil packaging includes the necessary lengths of 2000B Base, 2000C Hole Cut Cover, 2000WC Wire Clips, and 2001 Couplings for complete installation.

Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

	Plugmold 2000 Series Steel with Snapicoil Harness Ordering Information										
CATALOG NO.		NGTH	WIRING CONFIG	CENTEF	DUTLETS (15A 120V NEMA 5-15SR) CENTER DISTANCE QUANTITY Inches (mm)			CUT COV	HOUSING		
	Feet	(meters)		inches	(mm)			reet	(m)		
20GB12*	48'	(14.63)	GB	12"	(305mm)	48 Single	8	6'	(1.8m)	Steel – Ivory, Gray	
20GB18*	48'	(14.63)	GB	18"	(457mm)	32 Single	8	6'	(1.8m)	Steel – Ivory, Gray	
V20GB30	50'	(15.25)	GB	30"	(760mm)	20 Single	10	5'	(1.5m)	Steel – Ivory	
20GBA12*	48'	(14.63)	GBA	12"	(305mm)	48 Single	8	6'	(1.8m)	Steel – Ivory, Gray	

CUSTOM PLUGMOLD

Plugmold is one of our most frequently requested custom products. From airports, to trains, to classrooms, dormitories or residences, anywhere multiple access to power or USB charging is needed. Custom receptacle spacing options, custom colors, wiring modifications, or any number of custom configurations are available for special applications. Contact the factory to discuss our capabilities and why Plugmold is often the best option for locations requiring multiple access to power or USB charging.





Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

Description/Specifications

GFCI Plugmold

Product



GFCI Module provides downstream protection for all outlets and connections. Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm) receptacle spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor).
.040" (1.0mm) steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. GFCI Class A 20A 125V 60Hz.

CATALOG NO.	FINISH	LEI Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLETS QUANTITY & TYPI	
WH20GB306TRGFI6	White	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
BK20GB306TRGFI6	Black	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
V20GB306TRGFI6	lvory	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
G20GB306TRGFI6	Gray	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
S20GB306TRGFI6	Stainless	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
WH20GB506TRGFI6	White	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
BK20GB506TRGFI6	Black	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
V20GB506TRGFI6	lvory	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
G20GB506TRGFI6	Gray	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
S20GB506TRGFI6	Stainless	5'	(1.5m)	GB	6"	(152mm)	1 GFCI, 9 Single	15A
WH20GB606TRGFI6	White	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
BK20GB606TRGFI6	Black	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
V20GB606TRGFI6	lvory	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
G20GB606TRGFI6	Gray	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A
S20GB606TRGFI6	Stainless	6'	(1.8m)	GB	6"	(152mm)	1 GFCI, 11 Single	15A

NOTE: GFCI module does not contain an outlet.

Tamper-Resistant Plugmold





Receptacles prevent the accidental insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements. Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm) receptacle spacing. 15A tamper-resistant receptacles. | 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). .040" (1.0mm) steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.

CATALOG NO.	FINISH	LEI Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLE QUANTITY &	
WH20GB306TR	White	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
BK20GB306TR	Black	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
V20GB306TR	lvory	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
G20GB306TR	Gray	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
S20GB306TR	Stainless	3'	(915mm)	GB	6"	(152mm)	6 Single TR	15A
WH20GB506TR	White	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
BK20GB506TR	Black	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
V20GB506TR	lvory	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
G20GB506TR	Gray	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
S20GB506TR	Stainless	5'	(1.5m)	GB	6"	(152mm)	9 Single TR	15A
WH20GB606TR	White	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
BK20GB606TR	Black	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
V20GB606TR	lvory	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
G20GB606TR	Gray	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A
S20GB606TR	Stainless	6'	(1.8m)	GB	6"	(152mm)	11 Single TR	15A

NOTE: Color codes: "V" for lvory ScuffCoat⁻⁻⁻ finish, "BK" for Black ScuffCoat⁻⁻⁻ finish, "G" for Gray enamel finish, "WH" for white enamel finish, and "S" for stainless steel. Receptacle colors match extrusion colors except for stainless steel which has black receptacles and isolated ground versions which have orange receptacles.

All 2000 Series Plugmold products include two (2) 2010B Blank End Fittings and one (1) 2001 Base Coupling unless otherwise indicated in the product desciption.



Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

USB Plugmold





All USB Plugmold



Alternating **USB Plugmold** 3/4" [19.1mm] 19/32

NOTE: Color codes: "V" for Ivory ScuffCoat™ finish, "BK" for Black ScuffCoat™ finish, "G" for Gray enamel finish, "WH" for white enamel finish, and "S" for stainless steel. **Receptacle colors match extrusion** colors except for stainless steel which has black receptacles and isolated ground versions which have orange receptacles. All 2000 Series Plugmold products include two (2) 2010B Blank End

[32mm]

Fittings and one (1) 2001 Base Coupling unless otherwise indicated in the product desciption.

Available in 3' [914mm], 5' [1.5m] and 6' [1.8m] lengths with 6" [152mm] receptacle spacing. 15A tamperresistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor rated for use on 20A circuits). .040" [1.0mm] steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amp (shared between 2 ports) 5VDC.

USB PLUGMOLD		LE	ENGTH	WIRING	CENTER	DISTANCE	OUTLETS	
CATALOG NO.	FINISH	Feet	[mm]	CONFIG	Inches	[mm]	QUANTITY &	-
BK20GB306TRUSB	Black	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
BK20GB506TRUSB	Black	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
BK20GB606TRUSB	Black	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
G20GB306TRUSB	Gray	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
G20GB506TRUSB	Gray	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
G20GB606TRUSB	Gray	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
V20GB306TRUSB	lvory	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
V20GB506TRUSB	lvory	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
V20GB606TRUSB	lvory	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
S20GB306TRUSB	Stainless	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
S20GB506TRUSB	Stainless	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
S20GB606TRUSB	Stainless	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A
WH20GB306TRUSB	White	3'	[915mm]	GB	6"	[152mm]	1 USB A, 5 Single	15A
WH20GB506TRUSB	White	5'	[1.5m]	GB	6"	[152mm]	1 USB A, 9 Single	15A
WH20GB606TRUSB	White	6'	[1.8m]	GB	6"	[152mm]	1 USB A, 11 Single	15A

Available in 3' [914mm], and 5' [1.5m] lengths with 12" spacing. USB is 2.4 Amps (shared between two ports) 5VDC. .040" [1.0mm] steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. Each USB module provides 2 ports with 2.4 Amps of shared charging. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

ALL USB		LENGTH			CENTER	DISTANCE	
PLUGMOLD CATALOG NO.	FINISH	Feet	[mm]	WIRING CONFIG	Inches	[mm]	OUTLETS QUANTITY & TYPE
BK20USB312	Black	3'	[915mm]	USB	12"	[305mm]	3 USB A Modules
BK20USB512	Black	5'	[1.5m]	USB	12"	[305mm]	5 USB A Modules
G20USB312	Gray	3'	[915mm]	USB	12"	[305mm]	3 USB A Modules
G20USB512	Gray	5'	[1.5m]	USB	12"	[305mm]	5 USB A Modules
V20USB312	lvory	3'	[915mm]	USB	12"	[305mm]	3 USB A Modules
V20USB512	lvory	5'	[1.5m]	USB	12"	[305mm]	5 USB A Modules
S20USB312	Stainless	3'	[915mm]	USB	12"	[305mm]	3 USB A Modules
S20USB512	Stainless	5'	[1.5m]	USB	12"	[305mm]	5 USB A Modules
WH20USB312	White	3'	[915mm]	USB	12"	[305mm]	3 USB A Modules
WH20USB512	White	5'	[1.5m]	USB	12"	[305mm]	5 USB A Modules

Available in 5' [1.5m] length with 9" spacing, 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor rated for use on 20A circuits). .040" [1.0 mm] steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

ALTERNATING		LE	NGTH		CENTER DISTANCE			
USB PLUGMOLD CATALOG NO.	FINISH	Feet	[mm]	WIRING CONFIG	Inches	[mm]	OUTLETS QUANTITY & TYPE	
BK20GB509TRUSBA	Black	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
G20GB509TRUSBA	Gray	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
V20GB509TRUSBA	lvory	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
S20GB509TRUSBA	Stainless	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
WH20GB509TRUSBA	White	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/3 USB A Modules	
BK20GB509TRUAC	Black	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
G20GB509TRUAC	Gray	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
V20GB509TRUAC	lvory	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
S20GB509TRUAC	Stainless	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	
WH20GB509TRUAC	White	5'	[1.5m]	GB/USB	9"	[229mm]	3 Outlets/2 USB A & 1 USB C Modules	



WIREMOLD[°] Plugmold[°] Multioutlet Systems

Plugmold 2000 Series Steel Multioutlet Systems Ordering Information

	Cord-Ended Plugmold 2000 Series Steel Ordering Information									
CAT NO.	UNIT OUTLETS CIRCUIT CAT NO. LENGTH QUANTITY CORD SET LENGTH TYPE SWITCH BREAKER FINISH									
20-C2*	3' 4"	(1m)	6 Single	6'	(1.8m)	12/3 SJT	No	Yes	Steel – Gray, Ivory	

* Use "V" prefix for Ivory ScuffCoat" finish and "G" prefix for Gray enamel finish.

V2000BC (Ivory) WH2000BC (White) G2000BC (Gray) BK2000BC (Black) S2000BC (Stainless Steel)



V2000B-5 (Ivory) WH2000B-5 (White)

G2000B-5 (Gray)



V2000B-10 (Ivory) WH2000B-10 (White)



V2000C (lvory) WH2000C (White) G2000C (Gray)





620BCK

.040" (1.0mm) steel; 2000C Cover: .025" (.6mm) steel. Packed ten 5' (1.5m) lengths of each per carton.

Raceway Base - 040" (1.0mm) steel. Packed twenty 5' (1.5m)

Raceway Base - .040" (1.0mm) steel. Packed ten 10' (3.05m)

Raceway Cover - .025" (.6mm)

steel. Packed twenty 5' (1.5m)

lengths per carton. Has no

Raceway Base and Cover

Cutter - Portable cutter for

both 2000 Base and Cover.

receptacle hole cuts.

lengths per carton.

lengths per carton.

Base and Cover - 2000B Base:

1 5/16" (33mm)

W30/W30G



NOTE: Not for use with aluminum conductors.

2000WC



2001



V2003 (Ivory) 2003 (Plated Finish)



V2006 (Ivory) WH2006 (White) G2006 (Gray) BK2006 (Black) S2006 (Stainless Steel)



Pressure-Type Wire

Connectors – This part comes with both 16-W30 and 8-W30G. W30 – For common connection of two, three, or four No. 12 or No.14 solid copper conductors. W30G – For connection of equipment grounding of two, three, or four No.12 or No. 14 AWG solid conductors. 300V maximum; 20A 105° C maximum.

Wire Clip (Plated) – Use when conductors bypass receptacles. Not UL Listed.

Coupling (Galvanized Steel) - Joins lengths of 2000 Series Raceway Base.

2003 Supporting Clip -

Temporary support, while positioning lengths of raceway base. Use with 2000 Series Raceway.

- 1. 2003 mounted on surface with No. 6 flathead screw.
- 2. Plugmold 2000 snaps into 2003 Supporting Clip.

2006 Cover Clip – Covers seam where lengths of cover or base meet.

Replacement Blade Kit – Replacement blades and die set for 620 Cutter.



2000 Series Steel Raceway Fittings Ordering Information

2009



V2010A3 (lvory) WH2010A3 (White) G2010A3 (Gray) BK2010A3 (Black)



V2010A2 (Ivory) WH2010A2 (White) G2010A2 (Gray) BK2010A2 (Black) S2010A2 (Stainless Steel)



V2010B (Ivory) WH2010B (White) G2010B (Gray) BK2010B (Black) S2010B (Stainless Steel)



V2011 (lvory) WH2011 (White) G2011 (Gray) BK2011 (Black) S2011 (Stainless Steel)



Ground Clamp (Galvanized) – Connects equipment grounding conductor to provide an

additional ground to raceway.



2010A3 Entrance End Fitting – Offers larger capacity than V2010A2. 1/2" trade size KOs on end, each side and bottom. 3/4" trade size KOs on bottom and rear. Includes ground screw.



- Smallest entrance end fitting for connecting Plugmold 2000TR Series with 1/2" trade size conduit and armored cable connectors. 1/2" trade size KOs on end, each side and bottom. Includes ground screw.

Blank End - Closes off open

end of 2000 Series Raceway.

90° Flat Elbow - Right angle

turns on same surface. Cover

stop permits neat butting of

2000C Cover. Two couplings



V2015 (Ivorv)

2017TC



V2018C (lvory) WH2018C (White) G2018C (Gray) BK2018C (Black) S2018C (Stainless Steel)



V2048 (Ivory) WH2048 (White) G2048 (Gray) BK2048 (Black) S2048 (Stainless Steel)



Tee - Branches raceway at right angles. Couplings furnished.

Internal Corner Coupling – Furnished with one fiber bushing.



2017TC 2000B

1. 2017TC used as a corner coupling.

2. 2017TC used as a corner coupling and a straight-through fitting.

External Elbow Cover -

Continues raceway runs around outside corner. Fills the gap when external corner is made by notching and bending the 2000 Base.



Single-Gang Device Box – Cover has twistouts for 2000, 500 and 700 Series Raceways. Base has 1/2" trade size KO and rectangular KO for extension to wall box. Base has No. 10 threaded hole for ground connection.



furnished.



2000 Series Steel Raceway Fittings Ordering Information



2000 Series Interconnectivity Fittings

CONNECTIO		
FROM	ТО	USE CATALOG NUMBER
500 Series Raceway	Side of Plugmold 2000 Series	V2089, V2048, V2048-2
500 Series Raceway	End of Plugmold 2000 Series	V2089E, V2048, V2048-2
Existing Outlet	Plugmold 2000 Series	V2051H
1/2" trade size Conduit or Armored Cable	End of Plugmold 2000 Series	V2010A2, V2010A3





Plug-In Outlet Center Unit -

End Reducing Connector -

with 500 Series Raceway

Plugmold.

Connects 2000 Series Plugmold

through the end of 2000 Series

Six outlets, steel housing with ivory (V20-C2) or gray finish (G20-C2). 6' (1.8m) cord. Length 40" (1m). Receptacle center-tocenter 6" (152mm).



Plugmold 2400 Series Steel Multioutlet Systems

2400 Series Plugmold Wire Fill Capacities for Power									
CABLE	WIRE SIZE THHN/THWN	O. Inches	D.	NO. OF CONDUCTORS (40% FILL) 2400					
		inches	(mm)	2400					
POWER WIRING	10 AWG	0.166	(4.2)	26					
WITHOUT DEVICES	12 AWG	0.130	(3.3)	41					
	14 AWG	0.111	(2.8)	57					
POWER WIRING	8 AWG	0.218	(5.5)	2					
WITH DEVICES	10 AWG	0.153	(3.9)	6					
(Plugmold Series)	12 AWG	0.122	(3.1)	10					
	14 AWG	0.105	(2.7)	-					





	V	24	GBA	5	12
1	COLOR:	RACEWAY:	WIRING CONFIGURATION:	LENGTH:	CENTER DISTANCE
T	lvory = V	2400 = 24	$ \begin{array}{rcl} GB & = & \mathbf{GB} \\ GBA & = & \mathbf{GBA} \end{array} $	36" (915mm) = 3 60" (1.5m) = 5 72" (1.8m) = 6	6" (152mm) = 0 12" (305mm) = 1 10" (457mm)
100 Carias Steel Div	mald Cariaa w/D	unley Decenteele	Evennles 2460 BV2610	- ()	18" (457mm) = 1
100 Series Steel Plug	gmold Series w/D	uplex Receptacle -	- Example: 24SGBX3618		<u>9991V</u>
100 Series Steel Plug				I	<u>991V</u>

NOTE: Color codes: "V" for lvory ScuffCoat⁻⁻ finish. Receptacle colors match extrusion colors except for isolated ground versions which have orange receptacles.

* All 2400 Series Plugmold products include two (2) 2410B Blank End Fittings and one (1) 2401 Base Coupling unless otherwise indicated in the product desciption.



Plugmold 2400 Series Steel Multioutlet Systems Ordering Information

Product

Description/Specifications

Plugmold 2400 Series





Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm), 12" (305mm), 18" (457mm) and 24" (608mm) receptacle spacing. 20A receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and
insulated ground conductor)040" (1.0mm) steel housing. Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.

	CATALOG NO.	FINISH	LEI Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLET QUANTITY &	
	V24GB306	lvory	3'	(915mm)	GB	6"	(152mm)	6 Single	20A
	24S3612GBX99IV	lvory	3'	(915mm)	GB	12"	(305mm)	3 Duplex	20A
	24S3612GBA99IV	lvory	3'	(915mm)	GBA	12"	(305mm)	3 Duplex	20A
	V24GB506	lvory	5'	(1.5m)	GB	6"	(152mm)	10 Single	20A
	V24GB512	lvory	5'	(1.5m)	GB	12"	(305mm)	5 Single	20A
	V24GBA512	lvory	5'	(1.5m)	GBA	12"	(305mm)	5 Single	20A
)	24S6012GBX99IV	lvory	5'	(1.5m)	GB	12"	(305mm)	5 Duplex	20A
	24S6012GBA99IV	lvory	5'	(1.5m)	GBA	12"	(305mm)	5 Duplex	20A
	24S6012IGX99IV	lvory	5'	(1.5m)	IG	12"	(305mm)	5 Duplex	20A
	V24GB606	lvory	6'	(1.8m)	GB	6"	(152mm)	12 Single	20A
	V24GB612	lvory	6'	(1.8m)	GB	12"	(305mm)	6 Single	20A
	V24GBA612	lvory	6'	(1.8m)	GBA	12"	(305mm)	6 Single	20A
	V24GB618	lvory	6'	(1.8m)	GB	18"	(457mm)	4 Single	20A
	V24GBA618	lvory	6'	(1.8m)	GBA	18"	(457mm)	4 Single	20A
	24S7212GBX99IV	lvory	6'	(1.8m)	GB	12"	(305mm)	6 Duplex	20A
	24S7224GBA99IV	lvory	6'	(1.8m)	GBA	24"	(608mm)	3 Duplex	20A
	24S7218GBX99IV	lvory	6'	(1.8m)	GB	18"	(457mm)	4 Duplex	20A
	24S7224GBX99IV	lvory	6'	(1.8m)	GB	24"	(608mm)	3 Duplex	20A
	24S7218IGX99IV	lvory	6'	(1.8m)	IG	18"	(457mm)	4 Duplex	20A
	24S7212IGX99IV	lvory	6'	(1.8m)	IG	12"	(305mm)	6 Duplex	20A
	24S7224IGX99IV	lvory	6'	(1.8m)	IG	24"	(608mm)	3 Duplex	20A
	24S7212GBA99IV	lvory	6'	(1.8m)	GBA	12"	(305mm)	6 Duplex	20A
	24S7218GBA99IV	lvory	6'	(1.8m)	GBA	18"	(457mm)	4 Duplex	20A

NOTE: Color codes: "V" for Ivory ScuffCoat" finish. Receptacle colors match extrusion colors except for isolated ground versions which have orange receptacles.

All 2400 Series Plugmold products include two (2) 2410B Blank End Fittings and one (1) 2401 Base Coupling unless otherwise indicated in the product desciption.

2400 Series Plugmold Wiring Configurations								
			With S	napicoil				
GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.	IG Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated-isolated grounding conductor. Orange receptacles.	GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circui outlets wired alternately; has insulated grounding conductor				

NOTE: SNAPICOIL REELS on custom order. Snapicoil harness is available on reels if lengths greater than 50' are needed, or if multiple lengths are required for production-type jobs. The maximum length per reel is 240' for Snapicoil with outlets 12" and 18" on centers; 500' with outlets 30" on center. Packaging includes the necessary number of lengths of base, holecut cover, wire clips, and couplings for complete installation. Price and delivery information should be obtained prior to specifying or ordering. To specify or order, add "R" to the Snapicoil number. Ex: V24GB12R. Other outlet spacings available on custom order.

Receptacles are made from high impact thermoplastic. Snapicoil packaging includes the necessary lengths of 2400B Base, 2400C Hole Cut Cover, 2400WC Wire Clips, and 2401 Couplings for complete installation.



Plugmold[®] Multioutlet Systems

V2410C

V2411M

V2418M

2400 Series Steel Raceway Fittings Ordering Information



Base and Cover -

Base - V2400B .040" (1.0mm) steel. Cover - V2400C .040" (1.0mm) steel. Also available in custom colors.

Country of Origin: USA

Cross-Sectional Area: 1.39in² (897mm²)

ITEM	CAT. NO.	LE	NGTH	MATERIAL
Base	V2400B	5'	(1.5m)	.040 Steel
Cover	V2400C	5'	(1.5m)	.025 Steel
Base & Cover	V2400BC	5'	(1.5m)	.025 Steel



Coupling - For joining lengths of raceway. Use with V2400 Series.

Country of Origin: USA



17/8

(48mm)

2 11/16"

(68mm)

Entrance End Fitting - Has 1/2" and 3/4" trade size KOs on end and bottom. Additional 1/2" trade size KO on sides.

^{2 1/8}" Country of Origin: USA (54mm)

90° Flat Elbow - For right angle turns on the same surface (nonmetallic cover).

Country of Origin: USA

Internal Elbow - For making internal 90° corners. All steel construction.

Country of Origin: USA

2400WC



Wire Clip - Holds conductors in place in raceway.

Country of Origin: USA



outside corners (nonmetallic cover). **Country of Origin: USA**

External Elbow - For covering



V2406



Cover Clip - For covering joint where lengths of cover or base adjoin. Use with V2400 Series (nonmetallic).

Country of Origin: USA

2409

V2410B

13/16 (30mm)



Ground Clamp - No. 10 ground screw provided. Use with V2400 Series Raceway.

Country of Origin: USA

V2410A 15/8" (41mm) (51mm) 1 3/16" (46mm)

V2400 with 1/2" trade size conduit and armored cable. Use with V2400 Series Raceway. è

Country of Origin: USA

Blank End - For closing open end of V2400 Series Raceway.

Entrance End - For connecting

Country of Origin: USA



V2448 V2448-2



Back Feed Fitting - For feeding 2400 Series Raceway from an existing outlet box. Equipped with 1/2" trade size male bushing and locknut washer for grounding.

Country of Origin: USA

Device Box - Base has 1/2" trade size KO and rectangular KO for extension to wall box. Has #10 threaded hole for ground connection. Cover has twistouts for 500/700 Series Raceway on each end and twistouts for 2400 Series Raceway on each side.

Country of Origin: USA

CAT. NO.	L	W	D	GANG #
V2448	4 5/8" (117mm)	2 7/8" (73mm)	1 3/4" (44mm)	1
V2448-2	4 3/4" (121mm)	4 3/4" (121mm)	1 3/4" (44mm)	2



4 3/4"

(121mm)

2 3/4" (70mm)

2400 Series Steel Raceway Fittings Ordering Information



Extra Deep Device Box – Base has rectangular knockout to enable extension from existing singlegang flush wall box and 1/2" and 1" concentric KOs. Cover has twistouts for 500/700 Series Raceway on each end and twistouts for 2400 Series Raceway on each side.

Country of Origin: USA

CAT. NO.	L	W	D	GANG #
V2444	4 5/8" (117mm)	2 7/8" (73mm)	2 3/4" (44mm)	1
V2444-2	4 3/4" (121mm)	4 3/4" (121mm)	2 3/4" (44mm)	2



Side Reducing Connector – For connecting V2400 Series Raceway with V500 Series Raceway.

Country of Origin: USA

624

624BCK



2400 and 2400BD Raceway & Cover Cutter – Portable cutter for 2400B and 2400BD Raceway and Cover. Tooled steel construction for clean and easy square cuts. Total manual operation.

Country of Origin: USA

Replacement Blade Kit – Replacement blades and die set for 624 Cutter.

Country of Origin: USA



Duplex Receptacle – 3-wire, 15A, 125V, NEMA 5-15R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

Country of Origin: USA



2686FO







IG2427GT



V2426 1 9/16" (40mm)



Duplex Receptacle – 3-wire, 20A, 125V, NEMA 5-20R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

Country of Origin: USA

FiberReady Transition Feed

Fitting – Eliminates offsetting V2400 in connecting with surface panel boxes. Has 3/4" and 1" concentric trade size KOs with 1" trade size KO elongated so adjustment from surface to center of bushing is 1" (25mm) minimum to 1 5/8" (41mm) maximum. Has twistouts for transition to Pancake 1500 and 2600 Series Raceway.

Country of Origin: USA

Isolated Ground Duplex Receptacle – 3-wire, 15A, 125V NEMA 5-15R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

Country of Origin: USA

Isolated Ground Duplex

Receptacle – 3-wire, 20A, 125V NEMA 5-20R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors.

Country of Origin: USA

Lamp Holder – Medium base lamp holder 660W, 250V. Black, general purpose phenolic.

Country of Origin: USA





Aluminum Plugmold[®] Multioutlet Systems

Aluminum Plugmold^{*} Multioutlet Systems offer an attractive choice for hospital and commercial labs, as well as for residential applications. The durable finish offers both aesthetics and corrosion resistance. Aluminum Plugmold Series is available in single and alternating circuits, with standard or isolated ground tamper-resistant receptacles. It can also be customized to meet virtually any job requirement.





The durable corrosion-resistant finish of Aluminum Plugmold Series makes it an ideal solution for use in laboratories.

Plu	Plugmold AL2000 Series Wire Fill Capacities for Power										
CABLE TYPE	WIRE SIZE THHN/THWN	O Inches	.D. (mm)	NO. OF CONDUCTORS (40% FILL) AL2000							
POWER WIRING WITHOUT DEVICES	8 AWG 10 AWG 12 AWG 14 AWG	0.216 0.166 0.130 0.111	(5.5) (4.2) (3.3) (2.8)	12 24 38 51							
POWER WIRING WITH DEVICES (Plugmold Series)	8 AWG 10 AWG 12 AWG 14 AWG	0.218 0.153 0.122 0.105	(5.5) (3.9) (3.1) (2.7)	- 3 6 8							

Plu	Plugmold AL2400 Series Wire Fill Capacities for Power										
CABLE TYPE	WIRE SIZE THHN/THWN	O Inches	.D. (mm)	NO. OF CONDUCTORS (40% FILL) AL2000							
POWER WIRING WITHOUT DEVICES	6 AWG 8 AWG 10 AWG 12 AWG 14 AWG	0.254 0.216 0.164 0.130 0.111	(6.5) (5.5) (4.2) (3.3) (2.8)	13 18 37 58 78							
POWER WIRING WITH DEVICES (Plugmold Series)	6 AWG 8 AWG 10 AWG 12 AWG 14 AWG	0.254 0.216 0.164 0.130 0.111	(6.5) (5.5) (4.2) (3.3) (2.8)	3 4 8 12 16							

Plugmold AL2000 Series Steel Multioutlet Systems Ordering Information



NOTE: AL2000 Series Aluminum Plugmold products are available in an anodized finish with gray receptacles.

* All AL2000 Series Plugmold products include two (2) AL2010B Blank End Fittings and one (1) AL2001 Base Coupling unless otherwise indicated in the product desciption.

Plugmold AL2000 Series Aluminum Multioutlet Systems Ordering Information

Description/Specifications

Plugmold AL2000 Series

Product

A PARTICIPACITY OF THE PARTICI



Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm), 12" (305mm) and 18" (457mm) receptacle spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.

CATALOG NO.	FINISH	LE Feet	NGTH (mm)	WIRING	CENTE Inches	R DISTANCE (mm)	OUTLETS QUANTITY & T	
			()			()		
AL20GB306TR	Aluminum	3'	(915mm)	GB	6"	(152mm)	6 Single	15A
AL20GB506TR	Aluminum	5'	(1.5m)	GB	6"	(152mm)	10 Single	15A
AL20GB512TR	Aluminum	5'	(1.5m)	GB	12"	(305mm)	5 Single	15A
AL20GB606TR	Aluminum	6'	(1.8m)	GB	6"	(152mm)	12 Single	15A
AL20GB612TR	Aluminum	6'	(1.8m)	GB	12"	(305mm)	6 Single	15A
AL20GB618TR	Aluminum	6'	(1.8m)	GB	18"	(457mm)	4 Single	15A
AL20GBA606TR	Aluminum	6'	(1.8m)	GBA	6"	(152mm)	12 Single	15A
AL20GBA612TR	Aluminum	6'	(1.8m)	GBA	12"	(305mm)	6 Single	15A
AL20GBA618TR	Aluminum	6'	(1.8m)	GBA	18"	(457mm)	4 Single	15A

Aluminum GFCI Plugmold



GFCI Module provides downstream protection for all outlets and connections. Available in 3' (914mm), 5' (1.5m) and 6' (1.8m) lengths with 6" (152mm) receptacle spacing. 15A tamper-resistant receptacles. 3-wire,#12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. GFCI Class A 20A 125V 60Hz.

CATALOG NO.	FINISH	LEI Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLETS QUANTITY & TYP	Ξ
AL20GB306TRGFI6	Aluminum	3'	(915mm)	GB	6"	(152mm)	1 GFCI, 5 Single	15A
AL20GB506TRGFI6	Aluminum	5'	(1.5mm)	GB	6"	(152mm)	1 GFCI, 9 Single	15A





Plugmold AL2000 Series Steel Multioutlet Systems Ordering Information

Product

Description/Specifications

Aluminum All USB Plugmold

Available in 3' (914mm), and 5' (1.5m) lengths with 12" spacing. USB is 2.4 Amps (shared between two ports) 5VDC. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings.

CATALOG NO.	FINISH	LEI Feet	NGTH (mm)	WIRING CONFIG	CENTER Inches	DISTANCE (mm)	OUTLETS QUANTITY & TYPE
AL20USB312	Aluminum	3'	(915mm)	USB	12"	(305mm)	3 USB Modules
AL20USB512	Aluminum	5'	(1.5m)	USB	12"	(305mm)	5 USB Modules



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral and insulated ground conductor). Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB Type-A Module is 2.4 Amps (shared between two ports) 5VDC. USB Type-C module is a single 30W Power Delivery port. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

CATALOG NO.	FINISH	LEN	GTH	WIRING	CENTER DISTANCE	OUTLETS
		Feet	(mm)	CONFIG	Inches (mm)	QUANTITY & TYPE
AL20GB509TRUSBA	Aluminum	5'	(1.5m)	GB/USB	9"(229mm)	3 Outlets/3USB Modules
AL20GB509TRUAC	Aluminum	5'	(1.5m)	GB/USB	9" (229mm)	3 Outlets/2 USB-AModules/ 1 USB-C Module

NOTE: AL2000 Series Aluminum Plugmold products are available in an anodized finish with gray receptacles. All AL2000 Series Plugmold products include two (2) AL2010B Blank End Fittings and one (1) AL2001 Base Coupling unless otherwise indicated in the product desciption.



1 7/16" (37mm)

> 1 1/8" (29mm)



AL2000/AL2400 Series Aluminum Raceway Fittings Ordering Information





WIREMOLD°

Plugmold[®] Multioutlet Systems

AL2000/AL2400 Series Aluminum Raceway Fittings Ordering Information



AL2043TR



In-line Receptacle - Two 15A, 120V U-ground factory wired receptacles. Couplings furnished. Receptacles are tamperresistant.

Country of Origin: USA

(73mm)

4 5/8" (117mm) 4 27/32" (121mm)

AL2047-2

13/8"

13/8"

(35mm)

(35mm)

1

2

Nonmetallic Plugmold[®] Multioutlet Assemblies

Nonmetallic Plugmold Mulitoutlet Systems provides a versatile solution for many applications. Plugmold sections offer single or alternating circuits, standard or isolated ground receptacles, and Snapicoil[®] harnesses of prewired receptacles or cord ended units.

Nonmetallic Plugmold has a textured ivory finish with duplex receptacles, and can be customized to accommodate virtually any application.



Nonmetallic Plugmold Multioutlet Systems are available in a variety of configurations.

Plugmold NM2000 Series Nonmetallic Multioutlet Systems

Plugmold NM2000 Series Wire Fill Capacities for Power								
CABLE TYPE	WIRE SIZE THHN/THWN	Inches	O.D. (mm)	NUMBER OF CONDUCTORS (40% FILL) NM2000/NM2400				
POWER WIRING WITHOUT DEVICES	10 AWG 12 AWG 14 AWG	0.164 0.130 0.111	(4.2) (3.3) (2.8)	15 31 45				
POWER WIRING WITH DEVICES (Plugmold Series)	10 AWG 12 AWG 14 AWG	0.153 0.122 0.105	(3.9) (3.1) (2.7)	- 8 * 8 *				

* Including one hot, neutral, and ground wire from the receptacle.





Plugmold NM2000 Series Nonmetallic Multioutlet Systems

	Plugmold NI	M2000 Series N	Nonmetallic Part Numbe	ering System	
NM2000 Series Nonm	etallic Plugmold	Series – Exampl	e: NM20GB306		
	<u>N M</u>	20	<u>G</u> B	3	06
1-0	COLOR:	AMPERAGE:	WIRING CONFIGURATION:	LENGTH:	CENTER DISTANCE:
T	Nonmetallic = NM	20 = 15A	GB = GB	48" (1.2m) = 4	9" (229mm) = 9
		24 = 20A	GBA = GBA	60" (1.5m) = 5	12" (305mm) = 12
			IG = IG *	72" (1.8m) = 6	18" (457mm) = 18
					30" (760mm) = 30
			ations, length, and center distand contact Wiremold Technical Sup		•

NOTE: NM2000 Series Nonmetallic Plugmold products are available in an ivory finish with ivory receptacles.

* All NM2000 Series Plugmold products include two (2) NM2010B Blank End Fittings unless otherwise indicated in the product desciption.

Plugmold NM2000 Series Raceway Wiring Configurations								
		With Snapicoil						
GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.	IG Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated-isolated grounding conductor. Orange receptacles.	GB Series: 3-wire, #12 THHN (1 hot, 1 neutral and 1 ground), 1 circuit; has insulated grounding conductor.	GBA Series: 4-wire, #12 THHN (2 hot, 1 neutral and 1 ground), 2 circuit; outlets wired alternately; has insulated grounding conductor.				

NOTE: SNAPICOIL REELS on custom order. Snapicoil harness is available on reels if lengths greater than 50' are needed, or if multiple lengths are required for production-type jobs. The maximum length per reel is 240' for Snapicoil with outlets 12" and 18" on centers; 500' with outlets 30" on center. Packaging includes the necessary number of lengths of base, holecut cover, wire clips, and couplings for complete installation. Price and delivery information should be obtained prior to specifying or ordering. To specify or order, add "R" to the Snapicoil number. Ex: NM20GB12R. Other outlet spacings available on custom order.

Receptacles are made from high impact thermoplastic. Snapicoil packaging includes the necessary lengths of NM2000B Base, NM2000C Hole Cut Cover, NM2000WC Wire Clips, and NM2001 Couplings for complete installation.

	Cord-Ended Nonmetallic Plugmold Multioutlet Systems									
CAT NO.	UNIT LENGTH	OUTLETS QUANTITY	CORD	SET LENGTH	TYPE	SWITCH	CIRCUIT BREAKER	HOUSING		
NM20-C3	3' (.92n	n) 3 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory		
NM20-C4	4' (1.2m) 4 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory		
NM20-C5	5' (1.5m) 5 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory		
NM20-C6	6' (1.8m) 6 Duplex	6'	(1.8m)	14/3 SJT	Yes	Yes	PVC-Ivory		

	Plugmold NM2000 Series Raceway with Snapicoil Harness									
CATALOG NO.	LENGTH	WIRING CONFIG	OUTLETS (15A 120V NEMA 5-15SR) CENTER DISTANCE QUANTITY			HOLE CUT COVER QUANTITY LENGTH			HOUSING	
NM20GB12	48'	GB	12"	(152mm)	24 Duplex	8	6'	(1.8m)	PVC-Ivory	
NM20GBA12	48'	GBA	12"	(305mm)	24 Duplex	8	6'	(1.8m)	PVC-Ivory	

Plugmold NM2000 onmetallic Multioutlet Systems Ordering Information

Product

Description/Specifications

Plugmold NM2000 Series

Available in 4' (1.2m), 5' (1.5m) and 6' (1.8m) lengths with 9" (229mm), 12" (305mm) and 18" (457mm) and 30" (762mm) receptacle spacing. 15A receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with two (2) Blank End Fittings.





CATALOG NO.	FINISH	LEN Feet	GTH (mm)	WIRING CONFIG	CENTEI Inches	R DISTANCE (mm)	OUTLETS QUANTITY & T	
NM20GB412	Nonmetallic	4'	(1.2m)	GB	12"	305mm)	4 Duplex	15A
NM20GBA412	Nonmetallic	4'	(1.2m)	GBA	12"	(305mm)	4 Duplex	15A
NM20IG412	Nonmetallic	4'	(1.2 m)	GB	12"	(305mm)	4 Duplex	15A
NM20GB512	Nonmetallic	5'	(1.5m)	GB	12"	(305mm)	5 Duplex	15A
NM20GB515	Nonmetallic	5'	(1.5m)	GB	15"	(381mm)	4 Duplex	15A
NM20GB530	Nonmetallic	5'	(1.5m)	GB	30"	(760mm)	2 Duplex	15A
NM20GBA512	Nonmetallic	5'	(1.5m)	GBA	12"	(305mm)	5 Duplex	15A
NM20IG512	Nonmetallic	5'	(1.5m)	IG	12"	(305mm)	5 Duplex	15A
NM20GB609	Nonmetallic	6'	(1.8m)	GB	9"	(229mm)	8 Duplex	15A
NM20GB612	Nonmetallic	6'	(1.8m)	GB	12"	(305mm)	6 Duplex	15A
NM20GB618	Nonmetallic	6'	(1.8m)	GB	18"	(457mm)	4 Duplex	15A
NM20GBA609	Nonmetallic	6'	(1.8m)	GBA	9"	(229mm)	8 Duplex	15A
NM20GBA612	Nonmetallic	6'	(1.8m)	GBA	12"	(305mm)	6 Duplex	15A
NM20IG612	Nonmetallic	6'	(1.8m)	IG	12"	(305mm)	6 Duplex	15A

Plugmold NM2400 Series



Available in 4' (1.2m), 5' (1.5m) and 6' (1.8m) lengths with 9" (229mm), 12" (305mm) and 18" (457mm) and 30" (762mm) receptacle spacing. 20A receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). Packed 2 per carton. Each unit supplied with two (2) Blank End Fittings.

CATALOG NO.	FINISH	LEN Feet	GTH (mm)	WIRING CONFIG	CENTEI Inches	R DISTANCE (mm)	OUTLETS QUANTITY & T	
NM24GB412	Nonmetallic	4'	(1.2m)	GB	12"	305mm)	4 Duplex	20A
NM24GBA412	Nonmetallic	4'	(1.2m)	GBA	12"	(305mm)	4 Duplex	20A
NM24GB512	Nonmetallic	5'	(1.5m)	GB	12"	(305mm)	5 Duplex	20A
NM24GB530	Nonmetallic	5'	(1.5m)	GB	30"	(760mm)	2 Duplex	20A
NM24GBA512	Nonmetallic	5'	(1.5m)	GBA	12"	(305mm)	5 Duplex	20A
NM24GB612	Nonmetallic	6'	(1.8m)	GB	12"	(305mm)	6 Duplex	20A
NM24GB618	Nonmetallic	6'	(1.8m)	GB	18"	(457mm)	4 Duplex	20A
NM24GBA612	Nonmetallic	6'	(1.8m)	GB A	12"	(305mm)	6 Duplex	20A

NOTE: NM2000 Series Nonmetallic Plugmold products are available in an ivory finish with ivory receptacles. All NM2000 Series Plugmold products include two (2) NM2010B Blank End Fittings and one (1) NM2001 Base Coupling unless otherwise indicated in the product desciption.



Plugmold NM2000 Series Nonmetallic Multioutlet Systems Ordering Information



Plugmold NM2000 Series Nonmetallic Multioutlet Systems Ordering Information



Wall Box Adapter – For feeding raceway from an existing wall outlet; horizontal applications. Provides complete access to wall box for connections.

Country of Origin: USA



NM2048

NM2048-2

Sure-Snap[®] Device Box –

Cover snaps onto base, no screws required. Cover has twistouts on all sides. Rectangular KO in base for extension to wall box.

Country of Origin: USA

CAT. NO.	L	W	D	GANG #
NM2048	4 3/4" (121mm)	3" (76mm)	13/4" (44mm)	1
NM2048-2	4 3/4" (121mm)	4 7/8" (124mm)	13/4" (44mm)	2

NM2027-15 NM2027-20



Replacement Receptacles – 15A and 20A replacement devices. 6" (152mm) wire leads each side. Used to replace faulty receptacles in Plugmold Strips, not for installation in blank raceway base.

Country of Origin: USA



Wall Box Adapter – For feeding raceway from an existing wall outlet; vertical applications. Provides complete access to wall box for connections.

Country of Origin: USA

NM2044



Extra Deep Device Box – For mounting power/ communication device when additional depth is required. Has combination twistouts for 2700, 2800, 2900, and NM2000.

Country of Origin: USA

CAT. NO.	L	W	D	GANG #
NM2044	4 3/4" (121mm)	3" (76mm)	2 3/4" (44mm)	1
NM2044-2	4 3/4" (121mm)	4 7/8" (124mm)	2 3/4" (44mm)	2

NOTE: NM2000 Series fittings work with both NM20 (15A) and NM24 (20A) Plugmold Multioutlet Systems.



NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

Canada 905.738.9195 www.legrand.ca

