



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN1410FC #14 Nyl FK Term *Panduit Corporation*

Catalog Number	PN1410FC
Manufacturer	Panduit Corporation
Description	The PN14-10F-C Pan-Term® Terminal Is A Nylon Insulated, Locking Fork Terminal With Narrow Tongue. The Locking Tongue Design Locks In Place For A Secure Connection. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0006 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#14

Material, Color, and Finish

Color	Blue
Finish	Tin-Plated

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	#14 NYL FK TERM
extra long description	PAN PN14-10F-C Pan-Term® PN14-10F-C
Long Description	The PN14-10F-C Pan-Term® Terminal is a nylon insulated, locking fork terminal with narrow tongue. The locking tongue design locks in place for a secure connection. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PN14-10F-C Fork Terminal, Blue, Nylon, 14-18 Awg,



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983803125
Manufacturers Part Number	PN1410FC
UPC	074983803125

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

Packaging

Carton	100
Weight Per each	0.0006

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	7/32
standard	UL Listed 587H E52164; CSA Certified LR31212
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)