



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PWP120277 277VAC 24VDC PWR PK Dual Voltage

Pass & Seymour/Legrand

Catalog Number	PWP120277
Manufacturer	Pass & Seymour/Legrand
Description	P&S Universal Voltage Power Pack
Weight per unit	0.3600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

body	Thermoplastic
load	120/230/277VAC
media	Yes
supply voltage	120/230/277VAC, 50/60Hz

Descriptions

Description	277VAC 24VDC PWR PK DUAL VOLTAGE
extra long description	P&S PWP120277 POWER PACK 120 230 27
Long Description	P&S Universal Voltage Power Pack
Product Type	Power Pack 120 230 277VAC 24VDC
Special Features	Efficient switching power supply providing optimized current output based on number of sensors. Essential to ceiling mount sensor systems. Self-contained power supply relay system. UL2043 plenum rated for cost-effective installation. UL-rated 94 V0 plastic enclosure. 1/2" snap-in nipple attaches to standard electrical enclosures through 1/2" knockouts. LED indicates status of relay or low-voltage overcurrent. Secondary voltage: 24VDC;secondary output: 225mA. Easy to install. cULus listed. 5-year warranty.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007197808
Manufacturers Part Number	PWP120277
sub brand	Pass & Seymour
UPC	785007197808

Taxonomies, Classifications, and Categories

Category Description	TRANSFORMER ACCESSORIES
Type	Universal Voltage Power Pack

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	40
Package	1
Weight Per each	0.36

Uses, Certifications, and Standards

Application	Commercial
Enclosure	Thermoplastic, UL Flame Class Rating 94 V0
environmental conditions	Non-Condensing Relative Humidity 20 to 90
Mounting	JUNCTION BOX
Operating Temperature	0 to 35C
standard	UL, cUL, California Title 24 Compliant, RoHS-Compliant