Project	Ca	atalog #	Туре	
Prepared by	No	otes	Date	



# **HALO**

# **RA56 | Selectable CCT**

5"/6" All-purpose LED retrofit module with SeleCCTable switch

**Typical Applications** 

Residential

# Interactive Menu

- Order Information page 2
- Product Specifications page 2
- Photometric Data page 3
- Energy & Performance Data page 3
- Product Warranty

## **Product Certification**














rfer to ENERGY STAR® Certified Products List. In be used to comply with California Title 24 High Efficacy requirements. Intified to California Appliance Efficiency Database under JA8.

# **Top Product Features**



- Select from 5 CCTs via switch; 2700K, 3000K, 3500K, 4000K, 5000K CCT
- 600 lumen series
- · Use with 5" or 6" housings with screwbase adapter included
- · Dimmable down to 5%

# **Product Features**








# **Dimensional and Mounting Details**

# 7.25" [184.2mm]

## Scale



HALO

### Order Information

#### SAMPLE ORDER NUMBER: RA56069S1EWH

A complete luminaire consists of a housing, and LED module, order separately.

Models	Lumens	CRI/CCT	Driver	Finish
Models	Lumens	CRI/CCT	Driver	Finish
RA56 = 5"/6" LED Adjustable Gimbal	<b>06</b> = 600 lumens (nominal)	9S = 90 CRI minimum, white tuning, selectable CCT 2700K-5000K	<b>1E =</b> 120V 60Hz leading or trailing edge phase cut 1% dimming	WH = Matte white baffle

#### Housings

املا	۱.	ED	_	in	~1

H550ICAT = 5" LED, Insulated Ceiling, Air-Tite, New Construction

H550RICAT = 5" LED. Insulated Ceiling. Air-Tite. Remodel Housing E550ICAT = 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing E550RICAT = 5" LED, Insulated Ceiling, Air-Tite, Remodel Housing

H550FR2ICATD010= 5" fire safe new construction housing for phase-cut and 0-10V LED retrofit modules, 120-277V

#### Halo LED 6-inch

H750ICAT = 6" LED, Insulated Ceiling, Air-Tite, New Construction

H750RICAT = 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing H750T = 6" LED, Non-IC, Air-Tite, New Construction Housing H750TCP = 6" LED. Non-IC. New Construction/Remodel Chicago Plenum

H2750ICAT = 6" LED, Shallow, Insulated Ceiling, Air-Tite, New Construction (use with 691X, 694X, 696X trims only) H2750RICAT = 6" LED, Shallow, Insulated Ceiling, Air-Tite, Remodel (use

with 691X, 694X, 696X trims only) E750ICAT = 6" LED, Insulated Ceiling, Air-Tite, New Construction Housing E750RICAT = 6" LED, Insulated Ceiling, Air-Tite, Remodel Housing

 $\mbox{H750FR2ICAT}$  = 6" IC, airtight, 2 hour fire rated, new construction housing, LED, 120 - 277V

#### **Halo Shallow Housings 5-inch**

H25ICAT = 5" Shallow, Insulated Ceiling, Air-Tite New Construction H25RICAT = 5" Shallow, Insulated Ceiling, Air-Tite Remodel H25ICATNB = 5" Shallow, Insulated Ceiling, Air-Tite New Construction,

#### Halo Shallow Housings 6-inch

H27ICAT = 6" Shallow, Insulated Ceiling, Air-Tite New Construction H27RICAT = 6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing H27T = 6" Shallow, Non-IC, New Construction Housing

H27RT = 6" Shallow, Non-IC, Remodel Housing

E27RTAT = 6" Shallow, Non-IC, Remodel Housing

E27ICAT = 6" Shallow, Insulated Ceiling, Air-Tite New Construction E27RICAT = 6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing E27TAT = 6" Shallow, Non-IC, New Construction Housing

#### **Halo Standard Housings 5-inch**

H5ICAT = 5" Insulated Ceiling, Air-Tite New Construction Housing H5RICAT = 5" Insulated Ceiling, Air-Tite Remodel Housing H5ICATNB = 5" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket

H5T = 5" Non-IC. New Construction Housing

H5RT = 5" Non-IC. Remodel Housing

H5TNB = 5" Non-IC, New Construction Housing, No Socket Bracket ESICAT = 5" Insulated Ceiling, Air-Tite New Construction Housing

E5RICAT = 5" Insulated Ceiling, Air-Tite Remodel Housing ESICATNB = 5" Insulated Ceiling, Air-Tite New Construction Housing, No

Socket Bracket ESTAT = 5" Non-IC. New Construction Housing

E5RTAT = 5" Non-IC, Remodel Housing ESTATNB = 5" Non-IC, New Construction Housing, No Socket Bracket

H7ICAT = 6" Insulated Ceiling, Air-Tite New Construction Housing

H7RICAT = 6" Insulated Ceiling, Air-Tite Remodel Housing H7ICT = 6" Insulated Ceiling, New Construction Housing

H7RICT = 6" Insulated Ceiling, Remodel Housing

H7ICATNB = 6" Insulated Ceiling, Air-Tite New Construction Housing, No

H7ICTNB = 6" Insulated Ceiling, New Construction Housing, No Socket

H7T = 6" Non-IC, New Construction Housing

H7RT = 6" Non-IC, Remodel Housing

H7TNB = 6" Non-IC, New Construction Housing, No Socket Bracket H7TCP = 6" Non-IC, Chicago Plenum, New Construction/Remodel

H7UICAT = 6" Insulated Ceiling, Universal, Air-Tite, New Construction Housing

E7ICAT = 6" Insulated Ceiling, Air-Tite New Construction Housing

E7RICAT = 6" Insulated Ceiling, Air-Tite Remodel Housing

ETICATNB = 6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket

E7TAT = 6" Non-IC, New Construction Housing

E7RTAT = 6" Non-IC, Remodel Housing

E7TATNB = 6" Non-IC, New Construction Housing, No Socket Bracket

# **Product Specifications**

#### **CCT Select System**

· Use the switch to choose between 2700K, 3000K, 3500K, 4000K, and 5000K CCT.

#### Module - Trim

- Module construction includes LED array, heat sink, reflector, lens, baffle and trim ring.
- · Regressed baffle
- · Heat sink designed to conduct heat away from the LED array, keeping the junction temperatures below specified maximums, even when installed in insulated ceiling environments.

#### **LED Array**

- · Mid power LED array provides a uniform source with high efficiency and no pixilation.
- · 90 CRI minimum, R9 greater than 50
- · Color accuracy at 4 SDCM in between endpoints, provide color accuracy and uniformity.
- Color Temperature (CCT) has a selectable range from 2700K to 5000K (factory default 3000K)

#### **Optical Assembly**

- · Regressed lens
- · Impact-resistant polycarbonate
- · Convex form and lamp-like appearance
- · Diffuse for even illumination

- · Integral 120V 60 Hz constant current driver provides noise free operation
- Continuous, flicker-free dimming from 100% to 5%.
- · Inline electrical quick connect and E26 adapter (provided) provides mains connections
- · See Dimming Guide for compatible dimmers

#### Retention

- · Integral torsion springs and Push-N-Twist clips offer two mounting options
- · Torsion springs are pre-installed and adjust to fit 5" or 6" compatible housings
- · Push-N-Twist universal installation clips are preinstalled and designed to fit 5" or 6" compatible housings

#### Compliance

- UL Certified
- Damp location listed.
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy luminaire compliance. Complies with Title 24 JA8-2016-E.
- Can be used International Energy Conservation Code (IECC) high efficiency luminaire compliance.
- ENERGY STAR® listed, reference database for current listings

#### Warranty

· Five year limited warranty, consult website for details. www.cooperlighting.com/legal



## **Photometric Data**

RA56069S1EWHR-3000K				
Luminair	630			
Input	7.0			
LER (	90			
	0-180	1.21		
Spacing Criteria	90-270	1.21		
	Diagonal	1.29		
Beam angl	98.1			
Field angle	Field angle (degrees)			
Zonal lumen	Lumens	% Lumens		
0-30	201	31.9		
0-40	0-40 324			
0-60	532	84.5		
0-90	630	100		

<sup>\*</sup> Tested in accordance with IES LM63. Field results may vary.

# **Energy Data**

ENERGY DATA @ 3000K				
Lumens	600 Series			
Input Voltage	120V			
Input Current	.065 (mA)			
Input Power	7.0 (W)			
Efficiency	90%			
Inrush (A)	.91			
THD: ≤ 20%				
PF: ≥ 0.90				
T Ambient -30 - +40°C				
Sound Rating ≤ 20dba				

# **Product Specifications**

