



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HFD1020 HFD 1P 20A 65KA @277V Load Terms Only

Eaton Corp

Catalog Number	HFD1020
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, HFD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Single-Pole, 20 A, 347 Vac, 125 VDC, Load Side, 50/60 HZ
Weight per unit	1.7 (lbs/each)
Product Category	1 Pole

Features

Current Rating	20 A
dimensions	3.3800 IN X 1.3800 IN X 6.0000 IN
media	Yes
Poles	Single-pole
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	347 Vac, 125 Vdc

Descriptions

Description	HFD 1P 20A 65KA @277V LOAD TERMS ONLY
extra long description	ETN HFD1020 HFD, 1P, 20A, 65kA @277
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Single-pole, 20 A, 347 Vac, 125 Vdc, Load side, 50/60 Hz
Product Type	HFD, 1P, 20A, 65KA @277V, Load Term Only

Manufacturer Information

Brand	Eaton
GTIN	00786679175262
Manufacturers Part Number	HFD1020
UPC	786679175262

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.65

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed