



Mark 7 0-10V

MARK 7 0-10V IZT2S54D35M

The Mark 7 0–10V series of dimmable electronic ballasts offer maximum versatility by incorporating separate control leads for use with a wide array of controllers, including occupancy sensors, daylight harvesting controls, and building management systems from more than 40 manufacturers. When paired with linear fluorescent and 4-pin compact fluorescent lamps, these ballasts optimize the benefits of such popular sustainable lighting techniques as daylight harvesting, occupancy sensing, and load shedding to satisfy the need for an affordable, flexible and versatile controllable lighting solution.

Product data

General Information			
Lamp Type	F54T5HO		
Number Of Lamps	2 piece/unit		
Ballast Type	Dimmable Fluorescent		
Base Model	IZT2S24D		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical			
Input Voltage	120 to 277 V		
Input Frequency	50 to 60 Hz		
Total Harmonic Distortion USA	10 %		
Power (Rated) (Nom)	54 W		
Ignition Method	Programmed Start		
Crestfactor (Nom)	1.7		
Ignition Time (Nom)	1.5 s		
Ballast Factor (Max)	1.0		
Ballast Factor (Min)	0.03		
Power Factor (Nom)	0.98		

Input Current (Max)	0.38 A	
Input Current (Min)	0.91 A	
Input Power (Max)	118 W	
Input Power (Min)	16 W	
Rated Lamp Power	54W W	
Wiring		
Color Input Terminals	Black, White, Violet and Gray	

-			
Wiring			
Color Input Terminals	Black, White, Violet and Gray		
Color Output Terminals	RED, YEL & BLU		
Wire Striplength	0.375 mm		
Control Wire Gauge	18AWG		
Lamp Connection	Series		
Wire Length By Color	No wires		
Wire Gauge (Nom)	18AWG mm		
Wire Type	Solid		
Remote Wiring Configuration Allowed	No		
Tandem Wiring Configuration Allowed	No		
Through Wiring Configuration Allowed	Yes		
Max Ballast-Lamp Distance Remote Wiring	No Remote		


Datasheet, 2017, March 1 data subject to change

Mark 7 0-10V

Max Ballast-Lamp Distance Tandem Wirin	g No Tandem			
Max Ballast-Lamp Distance Through Wiring Any = 4'				
Connector Type	Poke-In			
Temperature				
T-Case Maximum (Nom)	70 °C			
Mechanical and Housing				
Housing Material	Metal			
Housing	D			
Housing Dimensions	16.7" x 1.18" x 1.0"			
Approval and Application				
EMC Immunity Standard	FCC Consumer			
Approval Marks	CSA certificate UL certificate CEC Listing RoHS			
	Compliant			

Hum And Noise Level	A			
UL Recognized	No			
Product Data				
Order product name	MARK 7 0-10V IZT2S54D35M			
EAN/UPC - Product	781087132159			
Order code	913701254102			
Numerator - Quantity Per Pack	1			
Numerator - Packs per outer box	12			
Material Nr. (12NC)	913701254102			
Net Weight (Piece)	441.000 g			

Dimensional drawing



ELE DIMMING BALLAS	Γ (2) F54T5HO 120-277V
ELE DIMINING DALLAS	1 (Z) F34 F3HO 1Z0-Z1 / V

Product	A1	A2	B1	C1
MARK 7 0-10V IZT2S54D35M	16.70 in	16.34 in	1.18 in	1.00 in

